

Philips
commercial TV

69 cm (27")
real flat

27HT7210D



Integrated Digital TV for entertainment and interactive services

Sleek and elegant RealFlat™ styling and integrated ATSC/QAM tuner provides superb picture quality with full commercial features. SmartPlug™ interface provides seamless pay-per-view connectivity and the ability to upgrade to new technology.

Vivid, natural and razor sharp images

- Real Flat picture tube technology brings you lifelike images

Interactive features

- SmartPlug Xpress & Serial Xpress Control interfaces
- Future proof by software upgradability

Reduced installation Time

- Wireless SmartLoader for fast cloning
- Total Program Control

PHILIPS
sense and simplicity

Specifications

Picture/Display

- Aspect ratio: 4:3
- Color cabinet: Silver Frost
- Diagonal screen size: 29 inch / 72 cm
- Picture enhancement: Scavem, AutoPicture (5 modes), Black stretch, Tint, Active Control, Comb Filter, Contrast Plus, Sharpness Adjustment, Smart Picture
- Visible screen diagonal (inch): 27 inch
- Display screen type: Real Flat picture tube

Sound

- Sound Enhancement: Auto Volume Leveller, AutoSound (4 modes), Incredible Surround
- Sound System: Incredible Surround, Stereo
- Output power (RMS): 2 x 5W

Convenience

- Remote Control: DVD, TV
- Clock: On/Off event timer, Sleep Timer
- On-Screen Display languages: French, Spanish, English
- User convenience: Closed Captioning (analog), Closed captioning (digital), Menu Languages, Vchip and parental lock
- Ease of Installation: Auto Volume Leveler
- Screen Format Adjustments: 4:3, 4:3 expand, 16:9 compress

Tuner/Reception/Transmission

- TV system: NTSC, ATSC
- Cable: Unscrambled Digital Cable -QAM
- Stereo System: BTSC
- Terrestrial: ATSC (8VSB)
- Video Playback: NTSC
- Aerial Input: 75 ohm F-type

Connectivity

- AV 1: CVBS in, Component Video in
- AV 2: CVBS, S-Video Y/C
- Front / Side connections: CVBS in, Headphone out
- Audio Output - Digital: AC3 over S/PDIF (Optical)
- AV 3: Monitor Out
- Connectivity Enhancements: External Loudspeaker connector, RJ12 SmartPlug connector, SmartCard Expansion Slot
- Other connections: Antenna F-type

Power

- Mains power: AC 90-140V, 60Hz

Dimensions

- Box dimensions in inch (W x H x D): 32.8 x 28.35 x 23.27 inch
- Product weight (lb): 96.8
- Set dimensions in inch (W x H x D): 28.98 x 22.83 x 19.29 inch
- Weight incl. Packaging (lb): 107.8

Highlights

Real Flat picture tube

The flatter tube provides a wider viewing angle while minimizing reflections for the best picture possible.

SmartPlug & Serial Xpress

The Smartplug interface permits OEM or 3rd party decoders and controllers to interface with the TV.

Upgradable software


The upgradable software architecture ensures that the TV is future proof and compatible with new technologies and developments, securing your investment.

Wireless SmartLoader

Provides the ability to copy easy and wireless all programming settings from one TV set into other TV sets in less than a minute. The feature ensures uniformity between TV sets and significantly reduces installation time and costs.

Total Program Control

Locks in commercial customized settings and features with a master TV set-up, significantly reducing installation time. Ensures uniformity across displays and prevents guests from altering pre-set formats.



Issue date 2011-06-07

Version: 4.0.9

12 NC: 8670 000 23825
UPC: 0 37849 96753 9

© 2011 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com