



Philips
Cordless telephone

CD230S

Cool comfort

Making a call with the CD2 series is as cool and relaxing as chatting with your best friend. The easy-to-handle handset with keypad & display backlight makes calling comfortable, wherever you are.

Pure convenience

- Display indicates the caller's name and number
- Backlit display & keypad
- An ergonomic shape gives you the most comfortable control

Clear calls around the house

- Virtually interference free
- Speakerphone - Talk handsfree
- Up to 300 m range to ensure a secure reception

PHILIPS
sense and simplicity

Specifications

Picture/Display

- Backlight
- Backlight color: Amber
- Display colors: Black & White
- Lines of text: 2
- Main Display Resolution: n.a. pixel
- Main Display Technology: CSTN
- Main Display Type: Alphanumerical

Sound

- Handset ringers: Instrumental, Polyphonic
- Volume Control: Volume Control up/down

Convenience

- Alarms: Alarm Clock
- Backlit keypad: Yes (Amber)
- Base Station keys: Paging key
- Battery charging indication
- Call Management: Call Waiting, Caller ID, Microphone mute
- Ease of Use: Hands free mode, Keypad Lock, Menu Control
- Function: Baby Call
- Multi base capability: Up to 4 bases
- Multi handset capability: Up to 4 handsets
- Signal strength indication

Dimensions

- Base dimensions: 125 x 118 x 56 mm
- Handset dimensions: 154 x 50 x 29 mm

Power

- Battery capacity: 650 mAh
- Battery type: AAA
- Battery Type: NiMH
- Kind of Battery: Rechargeable
- Mains power: AC 220-240V - 50Hz
- Number of batteries: 2
- Standby time: 120 hours
- Talk time: up to 10 hours

Network Features

- Antenna: Integrated on base, Integrated on handset
- Compatible: GAP
- Dialing: Tone, Pulse

Operator Requirements

- Name and Caller ID
- Caller ID on call waiting

Memory Capacity

- Call log entries: 20
- Phonebook: 50 names and numbers

Highlights

Caller name & number display

The name of the person or company calling is shown on the telephone display. The names of first-time callers can be displayed as well as those that are programmed into the telephone beforehand.

Backlit display & keypad

Backlit display & keypad ensures easy viewing and operation in low light conditions

Ergonomic Design

The smooth rounded shaped handset fits perfectly in your hand for natural, balanced operation. It looks great too!

Virtually interference free

Thanks to an advanced digital technology, calls are undisturbed by interferences from other devices.

Speakerphone - Talk handsfree

Handsfree mode uses a built-in loud speaker to amplify the voice of the caller, allowing you to speak and listen during a call without holding the phone to your ear. This is especially useful if you want to share the call with others or take notes during a call.

Up to 300 m range

Move freely in and around the house within a range of maximum 50 meters indoor and up to 300 meters outdoor (in ideal open-air conditions).



Issue date 2009-03-08

Version: 1.1.3

12 NC: 9961 400 05383
EAN: 87 10895 92884 7

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com