



Philips  
Cordless phone answer  
machine

CD6451B

## Enhanced Voice, Clear Colour

With voice clarity as clear as the bright colour screen, the CD6 series combines the best in voice and outstanding colour. An enhanced communication experience will delight users.

### Colours that bring your phone to life

- Icon-driven colour menu
- Bright colour display
- SMS text messaging

### Never miss a call

- 30-minute recording time
- Message-counter on Base
- Digital answering machine

### Natural voice clarity

- HD sound
- Speakerphone - Talk handsfree

**PHILIPS**  
sense and simplicity

# Specifications

## Picture/Display

- Backlight
- Backlight colour: White
- Main Display Resolution: 98x67 pixel
- Main Display Technology: CSTN

## Sound

- Handset ringers: Polyphonic
- Volume Control: Volume Control up/down

## Convenience

- Alarms: Alarm Clock
- Base Station keys: Answering machine keys, Paging key
- Battery charging indication
- Call Management: Call Waiting, Caller ID, Microphone mute
- Ease of Use: Graphical User Interface, Keypad Lock, Menu Control
- Function: Babysit function, Baby Call
- Multi base capability: 4
- Multi handset capability: Up to 5 handsets
- Personalisation/Customisation: Wallpaper
- Signal strength indication
- VIP group with own melody: Yes (3 groups)
- Backlit keypad: Yes (Amber)
- Speakerphone-Talk handsfree

## Network Features

- Antenna: Integrated on base, Integrated on handset
- Compatible: GAP

- Dialling: Tone, Pulse
- Messaging: SMS (Short Message Service)

## Operator Requirements

- Name and Caller ID
- Caller ID on call waiting

## Answering Machine

- Plug & Play Answering machine
- Recording time capacity: Up to 30 min.
- Message counter on base

## Memory Capacity

- SMS storage capacity: 50
- Call log entries: 50
- Phonebook: 200
- Number of SMS Boxes: 1

## Dimensions

- Base dimensions: 116 x 110 x 80 mm
- Handset dimensions: 46 x 26 x 160 mm

## Power

- Battery capacity: 750 mAh
- Battery type: AAA NiMH
- Kind of Battery: Rechargeable
- Mains power: AC 220-240V - 50Hz
- Number of batteries: 2 per handset
- Standby time: 150 hours
- Talk time: Up to 12 hours

# Highlights

## HD sound

Enjoy high quality conversation, with a level of clarity rarely heard before. Thanks to a high-quality speaker and to a real acoustic chamber, the audio spectrum reaches far beyond what's normally heard on a telephone.

## SMS text messaging

SMS (Short Message Service) lets you send and receive messages of limited length.

## Speakerphone - Talk handsfree

Handsfree mode uses a built-in loud speaker to amplify the voice of the caller, allowing you to speak and listen during a call without holding the phone to your ear. This is especially useful if you want to share the call with others or take notes during a call.



Issue date 2009-04-11

Version: 1.0.5

12 NC: 8670 000 26515  
EAN: 87 12581 30979 4

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)