



Philips  
Mobile Phone

692

CT0692BLK

## Compact design, smart messaging

The stylishly slim Philips 692 is a unique slider phone that puts smart handwriting recognition and multimedia functions – right at your fingertips. Enjoy the best of both worlds and easy navigation thanks to an intuitive touch-screen.

### Quick and easy messaging

- 2.4" Touch screen
- On-screen handwriting recognition
- Large 262K color TFT display for vivid, colorful graphics

### Maximize your Multimedia Experience

- Enjoy Bluetooth stereo music
- Video capture and playback in MPEG4 and H263 format
- Megapixel digital camera
- MicroSD memory card slot for extra memory/ data storage

**PHILIPS**  
sense and simplicity

# Specifications

## Dimensions

- Antenna: Integrated
- Handset color: Black
- Handset dimensions: 104 x 48 x 14.9 mm
- Form Factor: Slider
- Handset weight: 102g

## Picture/Display

- Diagonal screen size (inch): 2.4 inch
- Resolution: 240 x 320 pixels
- Main Display Colors: 262K
- Main Display Technology: TFT
- Touch panel

## Network Features

- GSM band: 900, 1800 MHz
- Messaging: Concatenated SMS (Long SMS), EMS / release 4, MMS, Multimedia Message Service, Predefined messages (SMS, MMS), SMS multi-target, WAP OTA provisioning
- Services: SIM Toolkit / Release 99
- Voice Codec: FR/AMR/HR

## Still Picture Capturing

- Digital zoom: x4
- Camera: Integrated
- Image sensor type: CMOS
- Picture Mode: Night mode, Self-timer mode, Continuous
- Picture resolution: VGA (640x480), QVGA (320x240), 120x160, SXGA (1280x1024)
- Special effects preview mode: Grey scale, Sepia, Embossed, Blue effect, Sketch, Blackboard, Whiteboard, Green effect, Blue carving, Color invert, Contrast, Copper carving, Gray invert, Normal
- White balance: Automatic, Cloudy, Incandescent, Fluorescent, Daylight, Tungsten
- Picture quality: Normal, High, Low

## Still Picture Playback

- Picture Compression Format: BMP, GIF (87a & 89a), JPEG

## Video Recording

- Compression formats: MPEG4, H.263
- Resolution (pxl): 160x120

## Sound

- Ringers: MP3 ringer, Polyphonic (64 tones)

## Audio Playback

- Audio supported formats: AMR, Midi, MP3

## Audio Capturing

- Voice recording: Yes, AMR

## Storage Media

- Built-in memory capacity: 11MB
- Maximum memory card capacity: 2 GB
- Memory Card Types: Micro Secure Digital (SD)
- Memory management: Memory status

## Convenience

- Buttons and controls: Soft keys, 4-way navigation keys
- Call Management: Call Cost, Call Forwarding, Call Time, Call Waiting, Caller ID, Emergency Call, Microphone mute, Missed Calls, Multi-party call, Received Calls
- Embedded Games: 2
- Clock/Version: International clock
- Ease of Use: Hands free mode, Softkeys, Vibrate Alert
- Games and applications: Alarm Clock, Calculator, Calendar, Stopwatch, ENG-CHN and CHN-ENG dictionary, Handwriting recognition, International converter, Female calendar, Weight management
- Language available: UI: Chinese Simplified, Chinese Traditional, English
- Personal Info Management: Time Zone, International clock
- Personalisation/Customization: Downloadable Picture, Downloadable Ringtones, Screen Saver, Wallpaper, Ringtones
- Vibrator

## Power

- Battery capacity: 900mAh
- Standby time: Up to 360 hours
- Talk time: Up to 3.5 hrs
- Battery Type: Li-ion

## Accessories

- Standard Package Includes: Battery, Charger, USB data cable, Deluxe stereo headset

## Connectivity

- Bluetooth
- Headset: Via mini USB connector
- Bluetooth profiles: A2DP, Headset, Object push profile

# Highlights

## 2.4" Touch screen

The easy-to-use touch screen gives you a simple and unique way to use your mobile phone and its stylus to quickly navigate menus, write SMS, personalize and give emotion to your pictures, play games, and access other applications

## Handwriting recognition

The intuitive and fast way to write text messages. Simply write on the touch screen as you would write on a piece of paper to have the phone convert your handwriting into an SMS (Short Message Service) text message. The feature has built-in handwriting recognition capability in both Chinese (traditional and simplified) and English (Roman alphabet).

## Large 262K color TFT display

Put the fun and excitement of the most vivid and colorful graphics and photos right at your fingertips with the large 262K color display that features excellent image quality and response time.

## Bluetooth stereo music

Your Philips mobile phone supports A2DP Bluetooth Profile. It lets you enjoy your favorite tunes wirelessly and in high quality stereo music from your Bluetooth headphones.

## Video capture and playback

The video capture function lets you record precious moments in MPEG4 or H263 format. Play it back on your phone or PC.

## Megapixel digital camera

The integrated digital camera with 1.3 megapixel resolution (1024x1280 pixels) allows you to capture precious moments of your life anytime, anywhere with your phone. Press camera key to take vibrant pictures and use as wallpaper and fotocall, or to send later via MMS.

## MicroSD memory card slot

You can now enjoy extra capacity and storage of multimedia files by inserting a MicroSD memory card into the built-in memory card slot of your phone.



Issue date 2009-07-02

Version: 2.0.1

12 NC: 8670 000 40184  
EAN: 87 12581 42739 9

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* Specification indicated based on initial full battery charge tested in laboratories with Bluetooth switched off. Actual performance is dependent on network service provider and usage.