

Philips  
Mobile Phone

968

CT9688



## Freestyle Messaging

Shoot and share videos

A great multimedia phone with camcorder and 1.3 Megapixel still camera plus TV Link to view your A/V footage and photo Thanks to the touch screen, you can tag photos with fun messages and easily enter SMSs in hand-writing recognition mode.

### Capture and share your life

- MPEG4 video recording
- 1.3 megapixel camera for clear, sharp picture quality
- TV Link to view a/v and slide shows
- SD card expansion slot

### Quick and easy messaging

- On-screen handwriting recognition
- Tag-It for fun and easy messaging
- Touch screen

### Maximize your Multimedia Experience

- Large 262K color TFT display for vivid, colorful graphics
- MP3 playback and ringtones for a superior audio experience

**PHILIPS**  
sense and simplicity

# Specifications

## Dimensions

- Handset weight: 128 g (with 900mAh batt.) 147 g (with 1450mAh batt.)
- Handset dimensions: 95 x 48.7 x 25 mm (with 900mAh batt.) 95 x 48.7 x 27.5 mm (with 1450mAh batt.)
- Handset volume: 115 cc (with 900mAh batt.) 127.2 cc (with 1450mAh batt.)
- Form Factor: Clam shell
- Antenna: Integrated
- Handset color: Titanium Tempo, Black Bass

## Picture/Display

- Main Display Technology: TFT
- Main Display Colors: 262K
- Resolution: 240 x 320 pixels (QVGA)
- Diagonal screen size (inch): 2.2 inch
- Touch panel

## Video Recording

- Compression formats: MPEG4
- Max resolution: QVGA pixel
- Resolution (pxl): 176x144, 320x240
- Recording system: NTSC

## Video Capturing

- Image sensor resolution: 1.3 M pixel
- Image sensor type: CMOS

## Video Playback

- Compression formats: 3GP

## Still Picture Capturing

- Camera: Integrated
- Picture resolution: 1.3M, VGA (640x480), QVGA (320x240), QQVGA (120x160)
- Digital zoom: x2, x4, x8
- Picture file format: JPEG
- Image sensor type: CMOS
- Picture Mode: Self-timer mode, Continuous
- Special effects preview mode: Sepia, B&W, Reversed, Vivid, Neutral, Cold
- White balance: Automatic, Sunny, Cloudy, Incandescent, Fluorescent, Night
- Picture quality: Normal, Fine, Superfine

## Still Picture Playback

- Picture compression format: BMP, GIF (87a & 89a), JPEG, PNG
- Picture enhancement: Tag it, Picture editor
- Slide show

## Sound

- Ringers: MP3 ringer, Polyphonic (64 tones), Voice memo ringer

## Audio Capturing

- Voice recording: Yes, AMR

## Audio Playback

- Audio supported formats: AMR, Midi, MP3

## Storage Media

- Built-in memory capacity: 64
- User memory: 40 MB
- Memory management: Memory status, Dynamic memory allocation

## Multimedia Applications

- Memory Card Access: SD card slot

## Network Features

- Messaging: E-mail, MMS, Multimedia Message Service, SMS multi-target, QQ instant messaging
- Services: SIM Toolkit / Release 99, WAP Browser Teleca2.0
- GPRS (Rx+Tx): Class 10 (4+2), Class B
- Voice Codec: FR/EFR/AMR
- GSM band: 900, 1800, 1900 MHz

## Convenience

- Call Management: Call Forwarding, Call Waiting, Caller ID, Conference Call, Emergency Call, Multi-party call
- Personal Info Management: Smart Phonebook
- Speech Recognition: Conversation Recording, Voice Memo
- Ease of Use: Hands free mode, Hot Keys, In-flight mode
- Ease of Navigation: Active swivel flip (DV/DC), Touch panel
- Swivel: 90 deg (DV/DC mode), 180 deg (Tablet Form)
- Buttons and controls: 4-way navigation key and enter, Camera key, Camera / Camcorder controls
- Games and applications: Agenda, Alarm Clock, Calculator, Java MIDP 2.0, Lunar Calendar, Countdown timer, Chinese festival reminder, ENG-CHN and CHN-ENG dictionary, Handwriting recognition
- Embedded Games: 4
- Clock/Version: International clock
- Stop watch
- Language available: T9 input: Chinese Simplified, Chinese Traditional, English
- Operating System: Linux OS
- Vibrator

## Connectivity

- Headset: Via bottom connector
- PC Link: USB 1.1
- Synchronisation PC organizer: MS Outlook

## Accessories

- Standard Package Includes: Charger, Stylus, USB data cable, Deluxe stereo headset, A/V TV Link
- Batteries: Li-ion 1450mAh batt. with SD slot Li-ion 900mAh batt (optional)

## Power

- Talk time: Up to 4 hrs
- Standby time: Up to 240 hrs
- Battery capacity: 1450 mAh
- Battery Type: Li-ion

# Highlights

## MPEG4 video recording

MPEG4 video recording lets you record your precious moments in high-quality MPEG4 video format with a selection of effects, then display in full-screen mode.

## 1.3 megapixel camera

Capture your most precious memories with the clearest, sharpest picture quality imaginable through stunning 1.3 megapixel resolution. Press camera side key to take vibrant pictures to use for wallpaper and fotocall, or to send later via MMS.

## TV a/v and slide show link

You can share the fun of viewing snapshots and videos with your friends and family by watching your clips on TV. Simply connect your phone to a TV via the TV-link cable to view your pictures and videos on the big screen.

## SD card expansion slot

Enjoy the convenience and fun of accessing more capacity to store pictures, videos and MP3 music files on your phone by inserting an SD card into the phone's built-in SD card slot.

## Handwriting recognition

The intuitive and fast way to write text messages. Simply write on the touch screen as you would write on a piece of paper to have the phone convert your handwriting into an SMS (Short Message Service) text message. The feature has built-in handwriting recognition capability in both Chinese (traditional and simplified) and English (Roman alphabet).

## Tag-it

Use Tag-It messaging to personalize and heighten the emotion of any picture with your own handwriting, drawings, or effects using the touch screen and integrated stylus, then easily share with friends via MMS (Multimedia Messaging Service) or infrared.

## Touch screen

Use the touch screen and integrated stylus to switch to an interface that is simple, intuitive, and comfortable to use. The easy-to-use touch screen lets you quickly navigate menus, write SMS, personalize and give emotion to your pictures, play games, and access other applications.

## Large 262K color TFT display

Put the fun and excitement of the most vivid and colorful graphics and photos right at your fingertips with the large 262K color display that features excellent image quality and response time.

## MP3 playback and ringtones

Use the data cable or an external memory card to transfer MP3 music files to your phone for a superior audio experience on the go. You can also personalize your ringtone with a selection from your MP3 files.



Issue date 2009-04-12

Version: 3.0.5

12 NC: 9961 400 04506

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)