



Philips Xenium
Mobile Phone

9@9m

Xenium

CT9A9MBRN

Incredible battery life

Tablet phone

With Philips Xenium 9@9m, enjoy the ease of multimedia messaging and real freedom of always being connected - thanks to an incredibly long battery life. Its ultra-intuitive touch screen and handwriting recognition keep you on the lead.

Always on, always connected

- Up to 1 month of standby time
- Up to 8.5 hours of talk time

Multimedia - anytime, anywhere

- MP3 playback and ringtones for a superior audio experience
- Video capture and playback in MPEG4 and H263 format
- 2 megapixel digital camera for crisp, vivid pictures
- Mini SD card expansion slot for extra memory/data storage

Quick and easy messaging

- 2.5" 262K color TFT display for vivid, colorful graphics
- On-screen handwriting recognition
- Touch screen

PHILIPS

sense and simplicity

Specifications

Power

- Battery capacity: 1280mAh Li-Polymer
- Standby time: Up to 1 month
- Talk time: Up to 8.5 hours
- Battery saving manager: Auto switch on/off

Picture/Display

- Diagonal screen size (inch): 2.5 inch
- Main Display Colors: 262K
- Main Display Resolution: 176x220 pixel
- Main Display Technology: TFT
- Touch panel

Dimensions

- Antenna: Integrated
- Form Factor: Candy bar
- Handset color: Executive silver, Rusted brown
- Handset dimensions: (105 x 50 x 17.3)mm
- Handset weight: 109g (With battery) / 78g (Without battery)

Network Features

- GSM band: 900, 1800, 1900 MHz
- Voice Codec: FR/EFR/AMR
- GPRS (Rx+Tx): Class 10 (4+2), Class B
- Messaging: Concatenated SMS (Long SMS), E-mail, EMS / release 4, MMS, Multimedia Message Service, SMS CB (Cell Broadcast), SMS (Short Message Service), SMS multi-target
- Services: OTA provisioning (WAP, MMS), SIM Toolkit / Release 99, WAP 2.0

Sound

- Ringers: MP3 ringer, Polyphonic (40 tones)

Still Picture Capturing

- Camera: Integrated
- Digital zoom: 8x
- Image sensor type: CMOS
- Integrated flash
- Picture resolution: VGA (640x480), 2M (1600x1200), 176x220, QVGA (320x240)
- Picture quality: Normal, Fine, Superfine
- Picture file format: JPEG
- Preview frame rate: 15 frames/second
- Picture Mode: Night mode, Self-timer mode, Multi-shot
- Special effects preview mode: Sepia, Negative color, B&W, Red effect, Sketch, Solarize

Video Playback

- Compression formats: MPEG4, H.263, 3GP
- Resolution (pxl): 176x144, 352x288, 320x240
- Frame rate (fps): 30

Video Recording

- Compression formats: 3GP
- Resolution (pxl): 176x144, 352x288
- Frame rate: 15 fps

Audio Playback

- Audio supported formats: AMR, Midi, MP3, SP-Midi

Audio Capturing

- Voice recording: Yes, AMR

Audio Recording

- Recording time: up to 30 minutes, up to 12 minutes per record

Convenience

- Buttons and controls: 4-way navigation key and enter, Camera key, Side keys, Soft keys
- Call Management: Call Cost, Call Counters, Call Forwarding, Call on Hold, Call Time, Call Waiting, Caller ID, Conference Call, Emergency Call, Explicit Call Transfer, Microphone mute, Missed Calls, Multi-party call, Received Calls
- Ease of Navigation: Animated Color Matrix, Touch panel
- Ease of Use: Hands free mode, Hot Keys, Keypad Lock, Screen Saver Digital Clock, Softkeys, Vibrate Alert
- Games and applications: Agenda, Alarm Clock, Calculator, Calendar, Java MIDP 2.0, Lunar Calendar, Chinese festival reminder, ENG-CHN and CHN-ENG dictionary, Handwriting recognition, International converter, Voice reminder if appointment, Sudoku game
- Language available: UI: Chinese Simplified, Chinese Traditional, English, Indonesian, Thai, Vietnamese
- Personal Info Management: Daylight saving, Time Zone, Smart Phonebook, Safeguard, International clock

Connectivity

- Headset: Via mini USB connector
- Modem Capabilities: CSD (Voice, Data), GPRS, SMS
- Wireless connections: Bluetooth, Infrared
- PC Link: USB 1.1
- Bluetooth profiles: A2DP, Handsfree, Headset, Object push profile

Storage Media

- User memory: 70 MB
- Memory Card Types: mini Secure Digital (SD)
- Memory management: Memory status, Dynamic memory allocation

Accessories

- Standard Package Includes: Battery, CD ROM (Mobile Phone Tools), Charger, Stereo Headset, Stylus, User Manual, USB data cable, Handset

Green Specifications

- Packaging material: Carton
- Packaging type: Giftbox
- Lead-free soldered product

Highlights

Up to 1 month standby time

The phone can be on and in standby mode continuously for up to 1 month on a single charge.

Up to 8.5 hours talk time

The phone can support up to 8.5 hours talk time on a single charge.

MP3 playback and ringtones

Use the data cable or an external memory card to transfer MP3 music files to your phone for a superior audio experience on the go. You can also personalize your ringtone with a selection from your MP3 files.

Video capture and playback

The video capture function lets you record precious moments in MPEG4 or H263 format. Play it back on your phone or PC.

Handwriting recognition

The intuitive and fast way to write text messages. Simply write on the touch screen as you would write on a piece of paper to have the phone convert your handwriting into an SMS (Short Message Service) text message. The feature has built-in handwriting recognition capability in both Chinese (traditional and simplified) and English (Roman alphabet).



Issue date 2009-04-28

Version: 1.0.2

12 NC: 8670 000 31674
EAN: 87 12581 34711 6

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com