



Philips
Portable Radio

DA1000



DAB & FM radio; more stations, digital sound

High quality digital audio

Tune into DAB and FM radio to enjoy a myriad of radio stations in crystal clear digital sound. DA1000 offers fast, precise tuning through 20 preset stations with a handy joystick - all packaged in a sleek, portable design.

Enjoy crystal clear digital radio

- Tune into near CD-quality radio stations
- DAB and FM compatible for a full radio experience
- EQ presets for your best listening in DAB mode

Long play time, rechargeable

- Enjoy playtime of up to 10 hours**
- Use built-in circuit to charge rechargeable batteries
- Large backlit LCD display for easier viewing in low light

Fast and accurate tuning

- Digital tuning with presets
- Autostore Programming for one-touch radio tuning
- Joystick control for easy navigation

PHILIPS
sense and simplicity

Specifications

Sound

- **Output power (RMS):** 3mW
- **Sound System:** Stereo
- **Volume Control:** Volume Control up/down

Audio Playback

- **Cassette Deck Technology:** Mechanical
- **Playback Media:** CD, CD-R, CD-RW
- **Disc Playback Modes:** Fast Forward/Reverse, Next/Previous Track Search, Repeat Play, Shuffle Play
- **Loader Type:** Top
- **Number of decks:** 1
- **Programmable Tracks:** 20

Tuner/reception/transmission

- **Antenna:** FM Antenna
- **Antenna location:** External
- **Auto digital tuning:** no
- **DAB:** Band III, EQ settings, Info display, Menu
- **Tuner Bands:** FM

Connectivity

- **DC in:** 6V
- **Headphones:** 3.5 mm

Convenience

- **Backlight**
- **Backlight colour:** White
- **Display Type:** LCD
- **Lines of text:** 2

Accessories

- **Included Accessories:** AC Power Lead, Battery, Charger, Headphones, Travel pouch, User manual, Warranty certificate

Dimensions

- **Packaging dimensions (W x H x D):** 223 x 273 x 68 mm
- **Product dimensions (W x H x D):** 60 x 111 x 21 mm
- **Weight:** 0.1 kg
- **Weight incl. Packaging:** 0.47 kg

Electricity

- **Adapter type:** 6V 300mA
- **Battery type:** AA, LR6
- **Battery voltage:** 1.5 V
- **Number of batteries:** 2

Product highlights

Near CD-quality radio stations

DAB and FM compatible

DAB (Digital Audio Broadcasting) digital radio is, in addition to FM analogue transmission, a new way of broadcasting radio via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in crystal clear, crackle-free sound quality. The technology allows the receiver to lock onto the strongest signal it can find. With DAB digital stations there are no frequencies to remember and sets are tuned by station name, so there is no returning on the move.

EQ presets for best listening

Up to 10 hours** playtime

Built-in recharge capability

Large backlit LCD display

Digital tuning with presets

Autostore programming

Autostore Programming is a convenient feature that allows you to tune in to your favourite stations and set station presets by simply pressing a button. Autostore Programming does away with the hassle of manual radio station tuning and setting of presets. A built-in electrical circuit automatically scans local radio station frequencies, locks on to the strongest radio station signals, and assigns them to specific presets.

Joystick control



Issue date 2009-02-12

Version: 2.0.3

12 NC: 9073 101 01315
EAN: 87 10895 82178 0

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com