

Philips
DVD player with USB

DivX

DVP3260



Straight from USB to TV

With Hi-Speed USB 2.0 Link

Your dream player with flawless, true-to-life picture quality and the ability to play virtually any disc! The Philips DVD player delivers your movies and music entertainment experience.



Brings audio and video to life

- 12-bit/108 MHz video processing for sharp, natural images
- 192 kHz/24-bit audio DAC enhances analogue sound input
- Progressive Scan component video for optimised image quality

Connect and enjoy multiple sources

- Hi-Speed USB 2.0 Link plays media from USB flash drives

Easy to use

- Create MP3s directly from CDs

Plays all your movies and music

- Plays DivX, MP3, WMA and JPEG digital camera photos
- Plays CD, (S) VCD, DVD, DVD+R/RW, DVD-R/RW
- DivX Certified for standard playback of DivX videos

PHILIPS

sense and simplicity

Specifications

Picture/Display

- **D/A converter:** 12-bit, 108 MHz
- **Picture enhancement:** Progressive Scan, Video upsampling

Sound

- **D/A converter:** 24-bit, 192 kHz
- **Frequency response:** 30-20,000 Hz
- **Signal to noise ratio:** > 100 dB
- **Distortion and Noise (1 kHz):** > 85 dB
- **Crosstalk (1 kHz):** > 100 dB
- **Dynamic Range (1 kHz):** > 90 dB
- **Sound System:** Dolby Digital

Video Playback

- **Playback Media:** CD, CD-R/CD-RW, Video CD/SVCD, DVD, DivX, DVD+R/+RW, DVD-R/-RW, DVD-Video
- **Compression formats:** MPEG1, MPEG2, DivX 3.11, DivX 4.x, DivX 5.x, DivX 6.0
- **Video disc playback system:** PAL, NTSC

Audio Playback

- **Playback Media:** CD, MP3-CD, MP3-DVD, WMA-CD, CD-R/RW, Audio CD
- **MP3 bit rates:** 32 - 320 kbps
- **Compression format:** MP3, Dolby Digital, PCM, WMA

Still Picture Playback

- **Playback Media:** DVD+R/+RW, DVD-R/-RW, CD-R/RW, Picture CD, Kodak Picture CD
- **Picture compression format:** JPEG
- **Picture enhancement:** Flip photos, Rotate, Zoom,

Slideshow

Multimedia Applications

- **Playback Formats:** DivX, JPEG Still pictures, MP3
- **Multimedia connections:** USB memory class device

Connectivity

- **Rear Connections:** Analogue audio Left/Right out, ComponentVideo out Progressive, Composite video (CVBS) output, Digital coaxial out, Scart
- **Front/Side connections:** USB

Convenience

- **Child Protection:** Child Lock, Parental Control
- **On-Screen Display languages:** English

Power

- **Power consumption:** < 10 W
- **Power supply:** 50 Hz, 240 V
- **Standby power consumption:** < 1 W

Accessories

- **Included Accessories:** 2 x AAA Batteries, Remote Control, World Wide Warranty leaflet, User manual

Dimensions

- **Packaging dimensions (W x H x D):** 480 x 80 x 282 mm
- **Set dimensions (W x H x D):** 360 x 37 x 209 mm
- **Set weight:** 1.3 kg
- **Weight incl. Packaging:** 2.4 kg

Product highlights

Plays it all

Play virtually any media format you want - whether it is DivX, MP3, WMA or JPEG. Experience the unbeatable convenience of great playability, and the luxury of sharing media files on your TV or home theatre system - in the comfort of your living room.

192 kHz/24-bit audio DAC

192 kHz sampling enables you to have an accurate representation of the original sound curves. Together with a 24-bit resolution, more information is captured from the original analogue sound wave form, giving a much richer audio reproduction.

Progressive Scan

Progressive Scan doubles the vertical resolution of the image resulting in a noticeably sharper picture. Instead of sending a field comprising the odd lines to the screen first, followed by the field with the even lines, it writes both fields at the same time. A full image is created instantaneously, using the maximum resolution. At such a speed, your eye perceives a sharper picture with no line structure.

Create MP3s

Convert the contents of your favourite CDs to MP3 files on your Philips product, and store it directly on a thumbdrive or on your portable media player through a USB cable. Enjoy the convenience of creating MP3 files right in your living room, without a PC, and even while the CD is playing.

Hi-Speed USB 2.0 Link

The Universal Serial Bus or USB is a protocol standard that is conveniently used to link PCs, peripherals and consumer electronic equipment. Hi-Speed USB devices have a data transfer rate of up to 480 Mbps - up from the 12 Mbps of original USB devices. With Hi-Speed USB 2.0 Link, all you have to do is plug in your USB device, select the movie, music or photo and play away.



Issue date 2009-02-11

Version: 4.0.14

12 NC: 8670 000 36033
EAN: 87 12581 38705 1

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com