

Philips
Steam iron



GC4610

Removes creases easily

Powerful ironing with SteamGlide soleplate

Ironing is smooth and effortless with this iron's SteamGlide soleplate. Its powerful steam and easy gliding make it the ideal combination to remove creases and get great results!

Powerful performance

- 2400 Watt enables constant high steam output

Easily removes creases

- Continuous steam of up to 40 g/min for better crease removal
- Steam boost up to 160 g/min helps to remove stubborn creases

Comfortable ironing

- Extra-long 3 m cord for maximum reach
- Soft grip for lasting ironing comfort

Easy gliding on all fabrics

- SteamGlide soleplate for powerful steam and superb gliding

Reaches into tricky areas

- Steam tip lets you iron right into hard-to-reach areas

PHILIPS
sense and simplicity

Specifications

Accessories

- Cord binder for easy cord storage

Full control

- Temperature-ready light: Indicates when set temperature is reached
- Variable steam settings to suit every garment

Smooth gliding

- SteamGlide soleplate

Easily removes creases

- Continuous high steam for better crease removal: 40 g/min
- Steam boost for the most stubborn creases: 150 g/min
- Steam tip: For hard to reach areas
- Vertical steam: For hanging fabrics
- Fine spray: Fine spray evenly moistens the fabric

Comfortable ironing

- 360 degree swivel: Provides maximum freedom

- during ironing
- Drip-stop: Keeps your garment spotless while ironing
- Ergonomic soft grip for lasting ironing comfort
- The iron is suitable for use with tap water
- Extra-long cord for maximum reach: 3 m

Longer living

- Double Active Calc System: Prevents and flushes out scale particles

Fast and powerful ironing

- Power for quick heat-up and constant high steam: 2400 W

Technical specifications

- Voltage: 220-240 V
- Power: 2400 W
- Frequency: 50-60 Hz
- Water tank capacity: 350 ml

Highlights

Extra-long 3 m cord

With the extra-long 3 m cord, you can easily reach right up to the edges of your ironing board - and further!

SteamGlide soleplate



The specially designed soleplate combines small vents for superior gliding on all fabrics and large vents for powerful crease removal.

160 gr/min steam boost

Steam boost up to 160 g/min helps to remove stubborn creases.

