

Philips
Coffeemaker

HD7502



Drip stop

Cord storage

Original coffee, effortlessly

Today`s look timeless taste

Superior Aroma

- Keeps aroma in the jug
- For a fast and hot cup of coffee

Easy to experience

- Drip stop to interrupt the brewing whenever you like
- Cord storage
- 1.2L (10-15 cups)

PHILIPS

sense and simplicity

Specifications

General specifications

- Dish-washer-proof parts
- Detachable swing filter
- Cord storage

Technical Specifications

- Power: 1000 W
- Frequency: 50/60 Hz
- Voltage: 220-240 V
- Cord length: 0.88 m
- Brewing time: < 10 minute(s)
- Capacity: 1.2L/ 10-15 Litres / cups

Design specifications

- Materials: Polypropylene/ Glass jug
- Dimensions (L x W x H): TBD mm
- Weight (incl. Packaging): TBD kg
- Weight appliance: TBD kg
- Color

Accessories

- Aroma jug



Issue date 2009-02-09

Version: 3.1

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com