



Philips
Coffeemaker

1.3L 1000W



HD7583

Good coffee easily

holds 10 to 15 cups, compact design

Elegant metallic coffee maker for people who look for an easy to use and reliable coffeemaker. This coffeemaker offers good value for money. It has a smart and compact design for easy storage.

Easy to experience

- The translucent water tank shows the water in the tank
- Illuminated power switch
- Comfortable grip for a steady pour
- Dishwasher-proof parts for easy cleaning
- The drip stop prevents dripping coffee on the hotplate
- Detachable swing filter for easy handling

Compact Design

- 1.3L for 10 - 15 cups
- Cord storage



Translucent water tank



Illuminated power switch

Cord storage



Drip stop

PHILIPS
sense and simplicity

Coffeemaker
1.3L 1000W

HD7583

Specifications

General specifications

- Translucent water tank
- Illuminated power switch
- Dish-washer-proof parts
- Drip stop
- Detachable swing filter
- Cord storage
- Non slip feet

Technical Specifications

- Power: 1000 W
- Capacity: 1.3L / 10 - 15 Litres / cups
- Voltage: 220-240 V
- Frequency: 50/60 Hz
- Cord length: 0.88 m
- Brewing time: 9 minute(s)

Design specifications

- Color: Steel silver
- Bowl, cover, pusher: Plastic (polypropylene)
- Dimensions (L x W x H): 220*220*290 mm
- Weight (incl. Packaging): 1.94 kg
- Weight appliance: 1.42 kg

Accessories

- Jug



Issue date 2009-02-09

Version: 2.1

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com