

Philips  
Portable Media Center

30GB\*

PMC7230



## Enjoy your video and music on the go

Immerse yourself in movies and music with the truly portable 30GB PMC7230. View comfortably on the 3.5" LCD display or any TV-hassle free. Direct video recording and timer function ensure that you will not miss any of your favorite programs.

### Full multimedia entertainment – anytime, anywhere


- 3.5" LCD color display for viewing comfort
- Direct video recording
- Timer function to schedule TV recordings
- Enjoy movies, videos, music and pictures on the go
- View movies, videos and pictures on any TV

### Easy enjoyment, straight away

- Easy synchronization with Windows XP PC
- Familiar and friendly Windows controls
- PlaysForSure for the widest choice of online content

### Perfect companion on the go, every day

- Store up to 130 hours of video or 15000 songs
- Enjoy up to 3 hours of video and 16 hours of music playtime



**PHILIPS**  
sense and simplicity

## Specifications

### Picture/Display

- **Diagonal screen size (inch):** 3.5 inch
- **Resolution:** 320 x 240 pixels, 262K Color
- **Type:** LCD

### Sound

- **Equalizer settings:** Classic, Electronica, Hip Hop, Jazz, Pop, Rock
- **Equalizer:** 5-bands

### Headphones

- **Frequency response:** 3dB
- **Output power:** Max 8mW
- **Signal to noise ratio:** 82dB - 90dB
- **THD:** 0.5% - 1%

### Speaker

- **Frequency response:** 3dB
- **Output power:** Max 0.5W
- **Signal to noise ratio:** 65dB - 80dB
- **THD:** 0.5% - 12%

### Audio Playback

- **Compression format:** MP3, WMA
- **ID3 Tag support:** Album indication, Genre title, Track title and artist name
- **MP3 bit rates:** 32 to 320kbps and VBR
- **WMA bit rates:** 32 to 256kbps and VBR
- **WMA sample rates:** 16,22.05,32,44.1,48 KHz

### Video Playback

- **MPEG4 ASP:** up to 720x 480, 3Mbps with mp3 up to 320 kbps, 8~48kHz, up to 30fps stereo audio in .avi format.
- **MPEG4 SP:** up to 720 x 480,3Mbps with mp3 up to 320 kbps, 8~48 kHz, upto 30fps, stereo audio in .avi format.
- **WMV9 SP (QVGA):** up to 320 x 240, up to 850 kbps (max peak 1700), up to 30fps, with Windows Media Audio up to 128 kbps (max peak 256), 44.1 kHz, stereo audio in .wmv/asf format
- **WMV9 SP (Widescreen QVGA):** up to 480 x 270 up to 850 kbps (max peak 1700), up to 30fps, with Windows MediaAudio up to 128 kbps (max peak 256), 44.1kHz, stereo audio in .wmv/asf format

### Audio Recording

- **Bit rate:** 128kbps
- **Recording formats:** MPEG1 layer 3 (MP3)

### Video Recording

- **Audio format:** 128kbps, MP3, stereo audio
- **Compression formats:** MPEG4 Simple Profile
- **Frame rate:** 30 fps
- **Resolution (pxl):** 320x240(QVGA) or 640x480(VGA)

### Still Picture Playback

- **Picture compression format:** JPEG
- Slide show

### Storage Media

- **Built-in memory type:** Hard disk
- **Hard Disk Capacity:** 30 GB
- **Music memory capacity:** Upto 15,000 songs (WMA @ 64kbps)
- **Video memory capacity:** Upto 130 hours

### Connectivity

- **Headphone:** 3.5 mm
- **USB:** High speed USB 2.0
- AV In connection
- AV Out connection

### Accessories

- **AC/DC Adaptor/Charger:** AY4126
- **Headphones:** SHE2550
- **Pouch:** AY4244
- **CD-ROM:** With Software and User Manual
- **Printed User Guide:** Quick Start Guide
- **Audio/Video cable:** AY3931

### Software

- **PlaysForSure:** Audio Download, Audio Subscription, Video Download, Video Rental, Video Subscription
- Windows Media Player 10
- Arcsoft MediaConverter

### Green Specifications

- Lead-free soldered product

### System Requirements

- CD-ROM drive
- **Hard disk space:** 64MB (or higher)
- **PC OS:** Windows XP (SP2 or above)
- **Processor:** Pentium III 800MHz (or higher)
- **RAM memory:** 256MB (or higher)

### Power

- **Battery capacity:** 2400 mAh
- **Battery Type:** Li-ion
- **Playtime on internal battery:** Upto 3hrs video or 16hrs audio
- Rechargeable

### Dimensions

- **Master carton quantity:** 4
- **Master carton dimensions:** 232 x 326 x 163 mm
- **Master carton weight:** 4.155 kg
- **Packaging type:** D-box
- **Packaging dimensions (W x H x D):** 153 x 110 x 153 mm
- **Weight incl. Packaging:** 1 kg
- **Product dimensions (W x H x D):** 95 x 107 x 22 mm
- **Product weight:** 0.235 kg

## Product highlights

Timer to schedule TV recording

3 hrs video and 16 hrs music

View movies and pictures on TV



Issue date 2009-01-29

Version: 2.1.9

12 NC: 8670 000 25791  
UPC: 6 09585 12259 8

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* 1GB = 1 billion bytes; available storage capacity will be less.  
\* Rechargeable batteries have a limited number of charge cycles and may eventually need to be replaced. Battery life and number of charge cycles vary by use and settings.  
\* The PlaysForSure, Windows Media and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.  
\* Actual transfer speed may vary based on your operating system and software configuration.  
\* Storage capacity based on 500 kbit/second, QVGA video or 4 minutes per song and 64 kbps WMA  
\* Protected TV or video content or DVDs cannot be recorded