



Geared to go

With MP3, WMA and FM tuner

Ultra-rugged and wearable, the GoGear 512MB* SA261 is all you need to enjoy your favorite MP3 music on the go. Record from FM tuner, use the microphone for voice recordings or line-in to record from any source.

Your music - anytime, anywhere!

- MP3 and WMA playback
- Dynamic Bass Boost for deep and dramatic sound
- FM tuner for radio enjoyment
- Built-in mini SD memory slot for memory expansion

Record your favorite tunes

- Voice recording to take notes or record anything, anytime
- FM Recording to record your favorite radio programs
- Record directly to MP3 via analog or digital line-inputs

Easy, intuitive music experience on the go

- Navigation based on track, artist or playlist
- SuperScroll Navigation finds songs in a simple, fast way
- Language learning made easy through AB Repeat and bookmark

Philips GoGEAR
Flash audio player

512MB*

GoGEAR



SA261



PHILIPS

sense and simplicity

Specifications

Picture/Display

- Backlight color: White
- Resolution: 128 x 48 pixels
- Type: LCD

Sound

- Bass enhancement: Digital Bass Boost
- Channel separation: 50 dB
- Equalizer customizable
- Equalizer settings: Classic, Jazz, Pop, Rock
- Frequency response: 30 - 18 000 Hz Hz
- Signal to noise ratio: >80 dB
- Output power (RMS): 2 x 4 mW

Audio Playback

- Compression format: MP3, WAV, Windows Media™ Audio
- ID3 Tag support: Album title and artist name
- ID3-tag support
- MP3 bit rates: 8-320 kbps and VBR
- MP3 sample rates: 8, 11.025, 16, 22.050, 24, 32, 44.1, 48 kHz
- WMA bit rates: 5 - 192

Audio Recording

- Audio file format: MP3
- Line in: analogue

Audio Capturing

- Audio file format: WAV
- Built-in microphone: mono
- Voice recording: ADPCM

Storage Media

- Built-in memory capacity: 512*
- Built-in memory type: NAND Flash
- Memory Card Types: mini Secure Digital (SD)

Tuner/Reception/Transmission

- Auto store

- Tuner bands: FM
- Number of Preset Channels: 10
- Frequency range: 87.5 - 108 MHz

Connectivity

- Headphone: 3.5 mm
- USB: USB 2.0
- Line in

Accessories

- Cables: Line-in, USB
- Headphones: SHE775
- Quick start guide
- Armband

System Requirements

- CD-ROM drive
- Hard disk space: 50 MB
- PC OS: Windows 2000 (SP4 or above), XP (SP1 or above)
- RAM memory: 128 MB
- Sound card
- USB: Free USB port

Dimensions

- Box dimensions (W x H x D): 150 x 170 x 75 mm
- Master carton dimensions: 176 x 162 x 234 mm
- Master carton quantity: 3
- Packaging type: D-box
- Product dimensions (WxDxH): 43 x 23 x 97.5 mm

Power

- Battery type: AAA / LR03 Alkaline
- Battery Playing time (Tuner): Up to 10 hours*

Software

- Device manager
- Windows Media Player 9
- Windows Media Player 10

Highlights

Mini SD Expansion Slot

This special slot on your player accepts standard flash memory SD cards so you can expand additional memory on your player. Enjoy greater flexibility of increased storage capacity anytime and anywhere.

Voice recording

Voice recording converts your GoGear player into a handy dictation machine. Besides playing music or listening to radio, you can also record notes or reminders for work or school, record shopping lists and phone numbers – even song lyrics. By pressing the recording button and speaking into the built-in microphone, voice messages are compressed and stored in the built-in internal memory. Voice recording gives you a highly portable voice recorder allowing you to record anything, anytime and anywhere!

FM Recording

Enjoy your favorite FM radio programs whenever you like, as often as you like. Simply activate the record function when you hear your favorite radio programs, the player encodes the radio signal into WAV and stores the file into the FM recording folder under the Recording menu.

SuperScroll

For fast and precise navigation to your favorite song. Navigate through hundreds of songs easily and smoothly - or one at a time - in just a few seconds. You can choose to move through your playlist one song at a time or just press and hold down a little longer to SuperScroll swiftly to your desired track.



Issue date 2012-02-03

Version: 1.0.2

12 NC: 9073 101 02057
UPC: 0 37849 96122 3

© 2012 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com

* 1MB = 1 million bytes; available storage capacity will be less.

* Battery life varies by use and settings.

* Storage capacity based on 4 minutes per song and 64 kbps WMA or 128 kbps MP3 encoding.

* Windows Media and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.

* The PlaysForSure, Windows Media and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.

* Actual transfer speed may vary based on your operating system and software configuration.