



Philips LightLife
Torch

SFL5540



Brighten your life!

With this modern indoor torch

Whatever type of torch you want, the LightLife range perfectly responds to your needs. Made with quality materials, each torch is fitted with lighting technology for optimal beam intensity and lifetime.

Top Performance

- Torch operates 20 times longer
- Torch operates 20 times longer
- LED with 50,000 hour life makes replacement unnecessary
- Innovative LED technology with extremely long operating life

Ease of Use

- Pre-focused beam delivers optimal light output and focus
- Shock resistant housing withstands damage caused by shocks
- One-stop shopping includes 3x ExtremeLife AAA

Specifications

Power

- Batteries included
- Battery type: AAA/LR03 Alkaline
- Number of batteries: 3

Technical specifications

- Housing material: ABS and rubber
- Bulb type: LED
- Bulb voltage: 3.8 V

Green Specifications

- Packaging material: Box, PET
- Packaging type: Clam shell blister

Packaging dimensions

- Packaging dimensions (W x H x D):
15 x 32.9 x 4.6 cm
- Packaging dimensions (W x H x D):

- 5.9 x 13 x 1.8 inch
- Net weight: 0.12 kg
- Net weight: 0.265 lb
- Gross weight: 0.181 kg
- Gross weight: 0.399 lb
- Tare weight: 0.061 kg
- Tare weight: 0.134 lb

Outer Box

- Outer carton (L x W x H): 50.8 x 18.1 x 16.9 cm
- Outer carton (L x W x H): 20 x 7.1 x 6.7 inch
- Net weight: .72 kg
- Net weight: 1.587 lb
- Gross weight: 1.52 kg
- Gross weight: 3.351 lb
- Tare weight: 0.8 kg
- Tare weight: 1.764 lb

Highlights

0.5 Watt Nichia LED

Due to the low energy consumption of the LED, the torch can be operated for a longer time.

20 times longer operating time

LEDs consume much less energy than incandescent bulbs, so your batteries will last up to 20 times longer, saving you money on replacement of batteries.

50,000 hours LED life

Light source replacement is unnecessary due to the extremely long LED life.

Innovative LED technology

A Light Emitting Diode (LED) is an energy efficient improved lighting technology.

Pre-focused beam

Thanks to a pre-shaped lens and/or reflector the beam provides the optimal light output and focus.

Shock resistant

A special shock resistant plastic or rubber housing prevents damage to your torch caused by shocks.

3x ExtremeLife AAA included

The Philips batteries that are recommended for the product are enclosed in the packaging to make immediate use possible.



Issue date 2009-06-10

Version: 4.0.8

12 NC: 8670 000 29353
EAN: 87 12581 33118 4

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com