

Philips LightLife  
Torch

Rubber

SFL556 I



## Brighten your life!

With this shock- and waterproof outdoor torch

Whatever type of torch you want, the LightLife range perfectly responds to your needs. Made with quality materials, each torch is fitted with lighting technology for optimal beam intensity and lifetime.

### Top Performance

- Extremely low energy consumption
- Torch operates 20 times longer
- LED with 50,000 hour life makes replacement unnecessary
- Innovative LED technology with extremely long operating life

### Ease of Use

- Pre-focused beam delivers optimal light output and focus
- Rubber housing protects torch from splashing water
- Material to protect the torch from oil and grease
- Shock resistant housing withstands damage caused by shocks
- Nylon strap prevents you from losing your torch
- One-stop shopping includes 2x ExtremeLife AA

# PHILIPS

sense and simplicity

Torch  
Rubber

## Specifications

### Power

- Batteries included
- Battery type: AA/LR6 Alkaline
- Number of batteries: 2

### Technical specifications

- Housing material: Natural Rubber
- Bulb type: LED
- Bulb voltage: 3.2 V

### Green Specifications

- Packaging material: Box, PET
- Packaging type: Clam shell blister

### Packaging dimensions

- EAN: 87 12581 33122 1
- Number of products included: 1
- Packaging type: Blister
- Packaging dimensions (W x H x D): 12.8 x 26.8 x 5.9 cm

- Packaging dimensions (W x H x D): 5.0 x 10.6 x 2.3 inch
- Net weight: 0.165 kg
- Net weight: 0.364 lb
- Gross weight: 0.225 kg
- Gross weight: 0.496 lb
- Tare weight: 0.06 kg
- Tare weight: 0.132 lb

### Outer Box

- EAN: 87 12581 33123 8
- Number of consumer packages: 6
- Outer carton (L x W x H): 28.6 x 28.4 x 10.4 cm
- Outer carton (L x W x H): 11.3 x 11.2 x 4.1 inch
- Net weight: 0.99 kg
- Net weight: 2.183 lb
- Gross weight: 1.63 kg
- Gross weight: 3.593 lb
- Tare weight: 0.64 kg
- Tare weight: 1.411 lb

SFL5561/10

## Product highlights

### 3 \* (5MM) Nichia LED

*Due to the low energy consumption of the LED, the torch can be operated for a longer time.*

### 20 times longer operating time

*LEDs consume much less energy than incandescent bulbs, so your batteries will last up to 20 times longer, saving you money on replacement of batteries.*

### 50,000 hours LED life

*Light source replacement is unnecessary due to the extremely long LED life.*

### Innovative LED technology

*A Light Emitting Diode (LED) is an energy efficient improved lighting technology.*

### Pre-focused beam

*Thanks to a pre-shaped lens and/or reflector the beam provides the optimal light output and focus.*

### Splash waterproof

*Rubber sealing rings and housing prevent water causing damage to the torch and allow you to use it in all weather conditions.*

### Oil and grease resistant

*A rubber housing with a special coating to protect the torch from oil and grease.*

### Shock resistant

*A special shock resistant plastic or rubber housing prevents damage to your torch caused by shocks.*

### Nylon strap

*This strap makes the torch easy to carry around and prevents it from falling if it accidentally slips out of your hand.*

### 2x ExtremeLife AA included

*The Philips batteries that are recommended for the product are enclosed in the packaging to make immediate use possible.*



Issue date 2009-01-22

Version: 4.0.10

12 NC: 8670 000 29355  
EAN: 87 12581 33122 1

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)