



Philips  
In-Ear Headphones

SHE7750



## Turbo Bass

In-ear headphone with turbo-charged bass

High-quality in-ear headphones with turbo-charged bass

### Music to your ears

- 24 k gold-plated plug ensures an ultra-reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Neodymium magnet enhances bass performance and sensitivity
- Turbo Bass gives you superb deep and dynamic bass tones

### Made to fit you and your lifestyle

- 15 mm speaker driver optimises wearing comfort
- Asymmetric cable keeps the cable out the way

### Always ready to go

- A 1.2 m long cable that is ideal for outdoor use
- Durable Flexi-Grip makes a strong flexible connection
- Split cable enables convenient remote control connection

**PHILIPS**  
sense and simplicity

## Specifications

### Sound

- **Acoustic system:** Open
- **Magnet type:** Neodymium
- **Voice coil:** CCAW
- **Diaphragm:** Mylar dome
- **Frequency response:** 8 - 24 000 Hz
- **Impedance:** 16 Ohm
- **Maximum power input:** 50 mW
- **Sensitivity:** 108 dB
- **Speaker diameter:** 15 mm
- **Type:** Dynamic

### Connectivity

- **Cable Connection:** Two-parallel, asymmetric
- **Cable length:** 0.6 m + 0.6 m
- **Connector:** 3.5 mm stereo
- **Finishing of connector:** 24 k Gold-plated
- **Type of cable:** OFC

### Inner Box

- **Gross weight:** 0.53 kg
- **Inner carton (L x W x H):** 23.3 x 18.5 x 11.3 cm
- **Net weight:** 0.372 kg
- **Tare weight:** 0.158 kg

### Outer Box

- **Gross weight:** 9.44 kg
- **Outer carton (L x W x H):** 48 x 40 x 48 cm
- **Net weight:** 1.728 kg
- **Tare weight:** 7.712 kg

### Packaging dimensions

- **Packaging dimensions (W x H x D):** 9.9 x 22 x 2.9 cm
- **Gross weight:** 0.062 kg
- **Net weight:** 0.018 kg
- **Tare weight:** 0.044 kg

## Product highlights

### 24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

### CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

### Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

### Turbo Bass

The unique bass wave design "turbo-charges" the low tones by directing them towards your ears. The result is a fantastically realistic and more involved experience.

### 15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

### Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

### 1.2 metre cable

The ideal cable length to give you the freedom to put your audio device where you want.

### Flexi-Grip design

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

### Split cable

This standard cable has a 3.5 mm socket on one end and a 3.5 mm plug on the other for extending your freedom of movement with headphones.

