



Ultra sound

Three cap sizes for optimal fit

Revel in the ultra sound performance of the SHE 9500. With its exceptionally snug fit and powerful Neodymium speaker drivers you can enjoy the most outstanding sound performance an in-ear headphone can deliver.

Music to your ears

- Passive noise isolation for better sound at lower volume
- Neodymium magnet enhances bass performance and sensitivity
- Copper Cladded Aluminium Wire improves sound quality
- 24 k gold-plated plug ensures an ultra-reliable connection

Made to fit you and your lifestyle



- Three interchangeable rubber ear caps for optimal fit in all ears
- Ergonomically shaped headphone enhances user comfort
- Asymmetric cable keeps the cable out the way
- Super soft rubber caps for sensational comfort

Always ready to go

- Carry case protects your headphones when not in use
- A 1.2 m long cable that is ideal for outdoor use
- Durable Flexi-Grip makes a strong flexible connection
- Split cable enables convenient remote control connection

Philips
In-Ear Headphones

SHE9500



PHILIPS

sense and simplicity

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 6–23,500 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Speaker diameter: 10 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, asymmetric
- Cable length: 0.6 m + 0.6 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24 k Gold-plated
- Type of cable: OFC

Accessories

- Carrying case
- Extension cable

Inner Box

- Gross weight: 0.572 kg
- Inner carton (L x W x H): 23.3 x 18.5 x 11.3 cm
- Net weight: 0.414 kg
- Tare weight: 0.158 kg

Outer Box

- Gross weight: 10.397 kg
- Outer carton (L x W x H): 48.8 x 39.8 x 49.2 cm
- Net weight: 9.144 kg
- Tare weight: 1.253 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 10 x 22 x 3 cm
- Gross weight: 0.069 kg
- Net weight: 0.022 kg
- Tare weight: 0.047 kg

Highlights

Passive noise isolation

The perfect, snug fit inside your ear stops unwanted background noise detracting from the pure pleasure of your favourite music. This means you still enjoy the headphones' superb sound quality at lower volume settings and also benefit from a longer battery life.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

For optimal fit in all ears

With a choice of three interchangeable ear caps from size small to large, surely there is a pair that fits your ear perfectly.

Comfort fit

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

Super soft rubber caps

The ultra-soft rubber material on the rubber caps is sensational to the touch and adapts effortlessly to your ear. In-ear headphones have never been this comfortable.

Carry case

This case is the most convenient way to look after your headphones and prevent the cable tangling when not in use.

1.2 metre cable

The ideal cable length to give you the freedom to put your audio device where you want.

Flexi-Grip design

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

Split cable

This standard cable has a 3.5 mm socket on one end and a 3.5 mm plug on the other for extending your freedom of movement with headphones.



Issue date 2009-05-31

Version: 5.0.10

12 NC: 9082 100 04787
EAN: 87 10895 90382 0

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com