



Philips  
In-Ear Neckstrap  
Headphones




SHE9650

## Nano Lanyard

Designed for iPod Nano

Stay closer to your iPod nano and your favourite music with these lanyard-style headphones designed for iPod nano. The custom-made, secure connection ensures you won't miss a beat while you're on the move.



### Enjoy quality sound

- Perfect in-ear seal blocks out external noiseBlocks out exte
- Ultra small efficient driver for perfect fit, perfect sound
- Passive noise isolation for better sound at lower volume
- Neodymium magnet enhances bass performance and sensitivity
- Powerful microdrivers deliver the widest frequency range
- Turbo bass air vents for deepest and richest bass
- Acoustic vents for well-balanced, realistic sound

### Use them for longer

- Ultra soft strap material for extra wearing comfort
- Super soft rubber caps for sensational comfort
- Lightweight, soft lanyard provides lasting comfort

### Made to fit you and your lifestyle

- Nano-Link connector fastens your iPod securely to lanyard
- Smart lanyard for easy access to your iPod nano without tang

**PHILIPS**  
sense and simplicity

## Specifications

### Sound

- **Acoustic system:** Open
- **Magnet type:** Neodymium
- **Voice coil:** CCAW
- **Diaphragm:** Mylar dome
- **Frequency response:** 6 - 23 500 Hz
- **Impedance:** 16 Ohm
- **Maximum power input:** 50 mW
- **Sensitivity:** 102 dB
- **Speaker diameter:** 10 mm
- **Type:** Dynamic

### Connectivity

- **Cable Connection:** Two-parallel, symmetric
- **Cable length:** Neckstrap type
- **Connector:** 3.5 mm stereo
- **Finishing of connector:** 24k Gold-plated
- **Type of cable:** OFC

### Inner Carton

- **Gross weight:** .585 kg
- **Inner carton (L x W x H):** 23 x 20.9 x 11.3 cm
- **Nett weight:** .084 kg
- **Tare weight:** .501 kg

### Outer Carton

- **Gross weight:** 11.16 kg
- **Outer carton (L x W x H):** 48.2 x 44 x 49.2 cm
- **Nett weight:** 1.344 kg
- **Tare weight:** 9.816 kg

### Packaging dimensions

- **Packaging dimensions (W x H x D):** 10 x 22 x 3.1 cm
- **Gross weight:** .067 kg
- **Nett weight:** .014 kg
- **Tare weight:** .053 kg

## Product highlights

### Perfect in-ear seal

The Super-small 10 mm speaker drivers fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

### Ultra small efficient driver

This means you still enjoy the headphones' superb sound quality at lower volume settings, and also benefit from a longer battery life.

### Passive noise isolation

The perfect, snug fit inside your ear stops unwanted background noise detracting from the pure pleasure of your favorite music. This means you still enjoy the headphones' superb sound quality at lower volume settings, and also benefit from a longer battery life.

### Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

### Ultra soft strap material

The ultra soft strap is made from durable cotton, which has a soft-touch to the skin. This makes it extra pleasant to wear.

### Super soft rubber caps

The ultra soft rubber material on the rubber caps are sensational to the touch and adapts effortlessly to your ear. In-ear headphones have never been this comfortable.



Issue date 2009-02-03

Version: 3.1.8

12 NC: 8670 000 28822  
EAN: 87 12581 32831 3

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)