



Philips  
Headband headphones

SHL8500



## Lightweight comfort

### High-powered sound

Performance, practicality and design come together with these high-powered, lightweight and comfortable headband headphones. Take them everywhere for fantastic sound all the time.

#### Music to your ears

- Enjoy best-in-class performance and optimum sound quality
- 24 k gold-plated plug ensures an ultra-reliable connection
- Neodymium speaker drivers deliver pure balanced sound
- Open-type design for a spacious sound experience

#### Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort
- Comfort is enhanced for long-term use
- Ultra-soft headband cushions for supreme wearing comfort

#### Always ready to go

- A 1.5 m long cable that lets you put the player in your bag
- Extra portability provided by extra lightweight material

# PHILIPS

sense and simplicity

## Specifications

### Sound

- **Acoustic system:** Open
- **Magnet type:** Neodymium
- **Voice coil:** CCAW
- **Diaphragm:** Mylar dome
- **Frequency response:** 10–28,000 Hz
- **Impedance:** 32 Ohm
- **Maximum power input:** 50 mW
- **Sensitivity:** 105 dB
- **Speaker diameter:** 40 mm
- **Type:** Dynamic

### Connectivity

- **Cable Connection:** Single-sided
- **Cable length:** 1.5 m
- **Connector:** 3.5 mm stereo
- **Finishing of connector:** 24k Gold plated
- **Type of cable:** OFC

### Packaging dimensions

- **Packaging dimensions (W x H x D):** 19.6 x 24.7 x 5.7 cm
- **Gross weight:** 0.22 kg
- **Net weight:** 0.085 kg
- **Tare weight:** 0.135 kg

### Outer Box

- **Gross weight:** 7.4 kg
- **Outer carton (L x W x H):** 44.4 x 39.2 x 53.6 cm
- **Net weight:** 2.04 kg
- **Tare weight:** 5.36 kg

### Inner Box

- **Gross weight:** 1.61 kg
- **Inner carton (L x W x H):** 37.4 x 21.6 x 25.6 cm
- **Net weight:** 0.51 kg
- **Tare weight:** 1.1 kg

## Product highlights

### 24 k Gold-plated plug

*You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.*

### Ultra lightweight design

*The slim, lightweight, stainless steel headband is so light you'll hardly notice you're wearing it.*

### Comfortable to wear

*This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.*

### 1.5 metre cable

*The ideal length of cable to give you more freedom of movement and to choose where you carry your audio device.*



Issue date 2008-12-17

Version: 3.1.8

12 NC: 8670 000 28823  
EAN: 87 12581 32834 4

© 2008 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)