




Philips  
Hi-fi headphones

Powerful bass

SHP8500



## Dynamic hi-fi sound performance

Comfortable and fully adjustable headphones with neodymium speaker drivers deliver dynamic sound performance

### The perfect listening experience

- 40 mm speaker driver delivers sound without distortion
- The whole ear is covered to optimise sound quality
- High-quality Linear Crystal Oxygen-Free Copper cable

### You'll forget you're wearing them!

- Easy to adjust headband ensures optimum fit and comfort

### Always ready to go

- The 3 m-long cable is ideal for use with headsets
- Single-sided cable reduces tangling and improves comfort
- Gold-plated adapter for ultra-reliable connection

# PHILIPS

sense and simplicity

Hi-fi headphones  
Powerful bass

# Specifications

## Sound

- Acoustic system: open
- Magnet type: Neodymium
- Frequency response: 10–28,000 Hz
- Impedance: 32 ohm
- Maximum power input: 1500 mW
- Sensitivity: 106 dB
- Speaker diameter: 40 mm

## Connectivity

- Cable Connection: one-sided
- Cable length: 3 m
- Finishing of connector: Gold-plated

## Accessories

- Adapter plug: gold-plated 3.5 - 6.3 mm
- Included: Velcro cable strap

## Packaging dimensions

- Packaging dimensions (W x H x D):  
23.5 x 30.1 x 11 cm
- Gross weight: 0.56 kg

- Net weight: 0.29 kg
- Tare weight: 0.27 kg
- EAN: 87 10895 95747 2
- Number of products included: 1
- Packaging type: Carton

## Outer Carton

- Gross weight: 9.8 kg
- Outer carton (L x W x H): 52.8 x 38.5 x 61.1 cm
- Net weight: 3.48 kg
- Tare weight: 6.32 kg
- EAN: 87 10895 95749 6
- Number of consumer packages: 12

## Inner Carton

- Gross weight: 2.06 kg
- Inner carton (L x W x H): 34.5 x 25 x 28 cm
- Net weight: 1.68 kg
- Tare weight: 0.38 kg
- EAN: 87 10895 95748 9
- Number of consumer packages: 3

SHP8500/00

# Highlights

## 3 m cable

A handy cable length to make it easier for you to move around freely while using your headphones.

## 40 mm speaker driver

The 40 mm speaker driver is made of a composite Mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

## Single-sided cable

The cable is conveniently connected to just one side, considerably reducing the risk of tangling and simplifying winding the cable up for storage.

## Easy to adjust headband

The easy to adjust mechanism provides a comfortable, close fitting acoustic seal between the ear cushion and ear, ensuring optimal performance.

## Gold-plated adapter

Be assured of a perfect connection and high-quality sound regardless of whether your audio devices are fitted with 3.5 or 6.35 mm jack sockets.

## Full-size design

Full-size ear shells not only cover your whole ear for better sound quality, but also provide space for a larger, higher performance driver.

## LC-OFC cable

The extremely pure copper used for this cable minimises transmission losses and delivers superb signal quality to the headphone and pure sound to your ears.



Issue date 2011-11-03

Version: 4.0.6

12 NC: 9082 100 07803  
EAN: 87 10895 95747 2

© 2011 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)