

Philips
Wireless TV link

SLV3100



Share your satellite or subscription TV channels

without wires

Watch your TV programmes wirelessly on your second TV.

Watch and listen anywhere!

- Watch any video device on a second TV
- Works with DVD+RW/DVD/VCR/set-top box and many more
- Compatible with most video devices and brands

Operate your TV entertainment anywhere!

- Device can be operated in a closed cabinet
- Record any input source no matter what you are watching

Simple set-up and easy to use

- Less clutter, less fuss and no cable laying or drilling
- Wireless signal passes through walls and ceilings

PHILIPS
sense and simplicity

Specifications

Tuner/Reception/Transmission

- Antenna location: Picture & Sound: Internal, RC Extender: Internal
- TV system: PAL, SECAM
- Typical range indoors: 15-30 m
- Typical range outdoors: 100 m
- Supported IR carrier frequency: 32-40 KHz
- Frequency range: picture & sound: 2.4 GHz RC extender: 433 MHz MHz
- Remote control extender

Accessories

- AC/DC Adapter: 2x 9VDC, 300mA
- SCART duplicator: on SCART input cable

Dimensions

- Receiver dimensions (W x H x D): 144 x 41 x 91 mm
- Temperature (operation): +5 °C to +35 °C
- Transmitter dimensions (W x H x D): 144 x 41 x 91 mm

Power

- Power consumption: 7 W
- Power supply: AC/DC Adapter, 220-240 V

Receiver

- SCART out: CVBS out, Audio L+R out

Transmitter

- SCART 1: CVBS in, Audio L+R in

Highlights

Watch any device on a second TV

The wireless link uses standard SCART and cinch plugs that are used by almost every brand of audio/video device. If your device has one of these standard connectors it will work with the wireless link

Works with DVD and many more

Extend your possibilities for viewing movies, sports events, live performances and a range of TV channels anywhere in your home. The wireless TV link is suitable for transmission of AV content of all brands of PayTV and Pay-per-View decoders, satellite receivers, set-top boxes, DVD players, VCRs and camcorders.

Works with almost all brands

The wireless link uses standard SCART and cinch plugs that are used by almost every brand of audio/video device.

Operates in a closed cabinet

If you store your audio/video devices in a cabinet, you cannot operate these devices with a normal IR remote control. The Philips wireless remote control link allows you to operate these devices when the cabinet doors are closed thanks to an RF-based link that picks up the infrared signals of a remote control and translates them into RF. The receiver unit then translates them back to IR.

Record sources independently

You can record any A/V input source - regardless of what you are watching on your main TV or on your second TV - thanks to this record function. You simply instruct the transmitter box which device should be recorded on your VCR or DVD-R.

Wireless means no drilling

A 2.4 GHz wireless link between the receiver and transmitter means you don't have to lay cables or drill holes through walls.

Wireless passes through walls

There's no need to buy or rent duplicate A/V equipment. The wireless RF system extends your possibilities for viewing DVD movies and your favourite Satellite or TV channels anywhere in your home. With a range of up to 30 metres inside the house, it delivers high-quality video and stereo audio no matter where your second TV is located.



Issue date 2009-06-10

Version: 3.0.7

12 NC: 9082 100 04999
EAN: 87 10895 90446 9

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com