



Philips Prestigo  
Universal remote control

PRESTiGo

SRU8008

## Maximum functionality. Minimum fuss.

Full colour icons for easy navigation and selection. Control up to 8 devices, like TV, DVD(R)-HDD, VCR, Satellite, Tuner, Cable and more.

### Single control solution for most devices and brands

- One remote for your TV, VCR, SAT, DVD, Tuner, CD, AMP and Receiver
- Extensive infrared code database for most devices and brands

### Smart intuitive use

- Easy-to-read 1.4" colour LCD display
- Rotary cursor control for fast menu navigation
- Activities to control multiple devices with one button press
- LCD screen with backlighting for convenience in the dark

### Quick and easy setup

- No manual needed for setup
- Convenient IR learning from another remote
- Easily add and label extra functionality

**PHILIPS**  
sense and simplicity

# Specifications

## Convenience

- Universal IR database: TV, VCR, DVD, SAT, CABLE, CD/MD, RECEIVER, AMP, Home Theatre, DVR, AudioSet, DMR, DVB-T/S, DVDR, DVDR-HDD combo, DVD-VCR combo, Game, HTS, PC, Projector (IR), PVR, TAPE, Tuner, TV-DVD combo, TV-VCR combo, TV-VCR-DVD combo
- Number of activities: 8
- Programmable macros: Yes, 8
- Battery low indication
- Display Type: LCD
- Ease of Installation: Autosearch
- Number of keys: 45
- On-Screen Display languages: Dutch, English, French, German, Italian, Russian, Spanish
- Languages in manual: English, French, German, Dutch, Spanish, Portuguese, Italian, Russian, Turkish, Swedish, Norwegian, Finnish
- Scrollwheel

## Infrared Capabilities

- Operating distance: 33 ft (10 m)
- Learning IR codes
- Number of brands in database: Over 1100

- Carrier frequency range: 19 kHz - 455 kHz
- Transmission angle: 90 degree

## Power

- Number of batteries: 3
- Battery type: AA/LR6 Alkaline
- Battery saving manager: Auto switch on/off

## Outer Box

- Number of consumer packages: 2
- Gross weight: 1.22 kg
- Outer carton (L x W x H): 33 x 17.1 x 9.6 cm
- Net weight: 0.298 kg
- Tare weight: 0.922 kg

## Packaging dimensions

- EAN: 87 12581 40584 7
- Number of products included: 1
- Packaging type: Soother
- Type of shelf placement: Soother
- Packaging dimensions (W x H x D): 15.75 x 31.95 x 4.7 cm
- Gross weight: 0.535 kg
- Net weight: 0.149 kg
- Tare weight: 0.386 kg

# Highlights

## 1.4" colour display

A 1.4" (96 x 67 pixel) colour LCD display is foreseen to provide easy readability of the content on the screen.

## Intuitive rotary cursor

A cursor incorporating a rotary wheel enables you to navigate through the setup menu and the device pages, in both clockwise and anti-clockwise directions.

## Guided setup

Unlike other universal remote controls, where a 3-digit code needs to be input to identify a brand and device, this remote incorporates on-device step-by-step instructions for setting up your equipment, regardless of brand.

## Learning functionality

Learning functionality refers to the process through which a remote control captures and stores infrared signals from other remotes for later use. When device codes are not included in the on-board database, they can always be learned from the original remote, simply by pointing to it.

## Universal IR code database

A universal IR code database refers to a library of infrared codes built in to a particular remote. This feature allows a remote to control your equipment without needing to learn individual signals. Select the correct infrared code sets in the database for the devices you want to control to enable control of virtually every audio/video system element on the market today – regardless of model or brand.

## Add extra functionality

Improved way of adding and labelling functions makes it easier and faster to add extra functionality. So, no more missing functions.

## Activity-based user interface

Instead of operating your components one by one, activity-based control blends the most commonly used functions into activities such as "Watch a movie" or "Listen to CD". When a user selects 'watch a movie', rather than having the end user address each individual piece of equipment, such as DVD player, TV and multimedia receiver, one button holds all necessary commands to be able to start watching a movie: switch on the TV, switch on the amplifier and select the right input, switch on the DVD player and start playing.

## Backlight on screen

Backlighting is a feature that illuminates the LCD screen or keypad for use in the dark. The two most common types of backlighting are LED and electroluminescent (EL). Remotes backlit with LEDs are typically bright but uneven with a yellow or green colour, while EL panels are smooth with blue, white or green shades.



Issue date 2009-04-11

Version: 4.0.11

12 NC: 8670 000 38313  
EAN: 87 12581 40584 7

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)