




Philips 4100 series  
Ultra Slim LED TV with  
Digital Crystal Clear

**80 cm (32")**

LED TV  
DVB T/C/T2/T2-HD/S/S2



**32PHS4132**

## Ultra Slim LED TV

with Digital Crystal Clear

Stylish in design and great in value. The Philips 4100 TV with Digital Crystal Clear features HD picture quality, high contrast and clear sound reproduction. Experience effortless entertainment from this simple to use model.

### **The right features presented elegantly**

- Slim, refined stands communicate lightness

### **A clear, vivid picture every time**

- Digital Crystal Clear for precision you'll want to share
- LED TV for images with incredible contrast

### **Television viewing at your convenience**

- Two HDMI inputs and Easylink for integrated connectivity
- USB for multimedia playback

# PHILIPS

# Highlights

## Modern edge feet look

When setting out to create a new TV, our teams consider every aspect: from technology to design. Our new edge feet were engineered to create space beneath your TV where a traditional stand would normally sit, offering you a more immersive viewing experience. The effect? A TV that stands confidently with a nod to the future.

## Digital Crystal Clear

For natural looking pictures from any source, Philips created Digital Crystal Clear. Whether you're indulging in your favorite shows, movies, the news, or are simply having a few

friends over for a night in, you'll enjoy it all in optimal contrast, color and sharpness.

## LED TV



With LED backlight you can enjoy low power consumption and beautiful lines combined with high brightness, incredible contrast and vibrant colors.

## Two HDMI inputs with Easylink

Avoid cable clutter with a single HDMI cable to carry both picture and audio signals from your devices to your TV. HDMI uses uncompressed signals, ensuring the highest quality from source to screen. Together with Philips Easylink, you'll need only one remote control to perform most operations on your TV, DVD, Blu-ray, set top box or home theatre system.

## USB (photos, music, video)

Share the fun. Connect your USB memory-stick, digital camera, mp3 player or other multimedia device to the USB port on your TV to enjoy photos, videos and music with the easy to use onscreen content browser.

# Specifications

## Picture/Display

- Display: LED HD TV
- Panel resolution: 1366 x 768p
- Aspect ratio: 4:3/16:9
- Brightness: 280 cd/m<sup>2</sup>
- Picture enhancement: Digital Crystal Clear
- Diagonal screen size: 32 inch / 80 cm
- Peak Luminance ratio: 65 %

## Smart Interaction

- Program: Pause TV, USB Recording\*
- Ease of Use: One-stop Home button
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB
- Signal strength indication
- Teletext: 1000 page Hypertext
- Electronic Program Guide\*: 8 days Electronic Program Guid
- Screen Format Adjustments: Autozoom, Superzoom, Movie expand 16:9, Unscaled, 4:3, 16:9

## Sound

- Output power (RMS): 16W
- Sound Enhancement: Incredible Surround, Clear Sound, Auto Volume Leveller, Bass Control, Smart Sound

## Connectivity

- Number of HDMI connections: 2
- Number of USBs: 1
- Number of scarts (RGB/CVBS): 1
- Other connections: Common Interface Plus (CI+), Digital audio out (optical), Satellite Connector, Antenna IEC75, Audio in (DVI), Headphone out
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play

## Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1, HEVC (H.265)
- Subtitles Formats Support: .SMI, .SRT, .SSA, .SUB, .TXT, .ASS

- Music Playback Formats: AAC, MP3, WAV, WMA (v2 up to v9.2)
- Picture Playback Formats: JPEG, BMP, GIF, PNG

## Supported Display Resolution

- Computer inputs: up to 1920x1080 @ 60Hz
- Video inputs: 24, 25, 30, 50, 60 Hz, up to 1366x768p

## Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM

## Power

- Mains power: AC 220 - 240 V 50/60Hz
- Standby power consumption: <0.3W
- Off mode power consumption: 0.5 W
- Ambient temperature: 5 °C to 35 °C
- Power Saving Features: Auto switch-off timer, Eco mode, Picture mute (for radio)
- Energy Label Class: A+
- Eu Energy Label power: 31 W
- Annual energy consumption: 46 kWh
- Mercury content: 0 mg
- Presence of lead: Yes\*

## Dimensions


- Box dimensions (W x H x D): 798 x 520 x 140 mm
- Set dimensions (W x H x D): 726.5 x 425.36 x 81.8 mm
- Set dimensions with stand (W x H x D): 726.5 x 479 x 184.64 mm
- TV stand width distance: 343.57 mm
- Product weight: 4.8 kg
- Product weight (+stand): 4.85 kg
- Weight incl. Packaging: 6.7 kg
- VESA wall mount compatible: 100 x 100 mm

## Accessories


- Included accessories: Remote Control, 2 x AAA Batteries, Power cord, Quick start guide, Legal and safety brochure, Table top stand

## Connections

### Side



### Rear



Issue date 2019-06-18

Version: 6.3.1

12 NC: 8670 001 43548  
EAN: 87 18863 01100 3

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* EPG and actual visibility (up to 8 days) is country and operator dependent.

\* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

\* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

\* (Philips) only compatible with specific Philips player device.

\* This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.