

**Preliminary**

Philips  
Recessed spot light



**59441/31/C1**

## Essential lighting for a bright home

Illuminate your spaces with Philips Meson LED downlight, and enjoy soft, uniformly distributed light from a high quality diffuser and a LED light source. Installing this downlight fixture can be relatively easy and quick for homeowners.

### **Easy to Experience**

- Easy to mount

**PHILIPS**

## Характеристики

### Design and finishing

- Material: synthetics
- Color: white

### Extra feature/accessory incl.

- LED integrated
- Diffused light effect
- Photometric data available

### Product dimensions & weight

- Length: 9.5 cm
- Width: 9.5 cm
- Net weight: 0.055 kg
- Recessed distance: 4.6 cm
- Cut out length: 8.0 cm
- Cut out width: 8.0 cm

### Technical specifications

- Mains power: Range 220 V - 240 V, 50-60 Hz
- Number of bulbs: 15
- Wattage bulb included: 0.25 W

- Maximum wattage replacement bulb: 3.5 W
- Total lumen output fixture: 300 lm
- Fixture dimmable: No
- LED
- Lifetime up to: 15,000 hrs
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

### Packaging dimensions & weight


- Height: 9.7 cm
- Length: 9.6 cm
- Width: 5.2 cm
- Weight: 0.080 kg

### Miscellaneous

- Especially designed for: Functional, Living- & Bedroom
- Style: Functional
- Type: Recessed spot light

## Особенности

### Easy to mount



Lightstrips that can be mounted on any surface with its integrated adhesive strip.



Дата выпуска 2019-01-28  
Owner: no-reply@philips.com  
Версия: 1.0.1

12 NC: 9150 057 45301  
EAN: 69 47830 43949 2

Test leaflet, for internal use only!  
© 2019 Philips Lighting Holding B.V.  
Все права защищены.

Характеристики могут меняться без предварительного уведомления Торговые марки являются собственностью Philips Lighting Holding B.V.

[www.philips.com](http://www.philips.com)