

PHILIPS

Hair Dryer

5000 Series

2100W

ThermoShield technology

2x ionic care*

3 heat & 2 speed settings



BHD500/00



Fast drying with no heat damage** with ThermoShield technology

ThermoShield technology gives you ultimate protection from heat damage, by actively controlling the air temperature of the dryer to an optimum level.

ThermoShield technology

- ThermoShield technology for ultimate heat protection

Powerful drying

- Fast drying for professional results with 2100W

Care and protect


- 2x ionic care* for shiny, frizz-free hair

Beautifully styled hair

- Precise control with 6 heat and speed settings
- Cool Shot to set your style
- Slim nozzle for touch-ups and detailed styling

Highlights

ThermoShield technology



The overheat detect sensor actively optimizes and controls the air temperature, protecting your hair from damage** caused by overheating. Enjoy a stress-free drying experience with ThermoShield technology.

2100W of power



This 2100W professional hair dryer creates a powerful airflow. The resulting combination of power and speed makes drying and styling experience quicker and easier.

2x ionic care*



This powerful ionic system generates up to 40 million ions per drying session, intensifying your hair's shine. So you can enjoy glossy, frizz-free hair.

6 heat and speed settings



Easily pick the combination of heat and speed that works best for your hair and style. Six different settings ensure precise control for tailored styling.

Cool Shot



The Cool Shot button provides an intense burst of cool air. It is used after styling to finish and set the style.

14 mm styling nozzle



The slim nozzle precisely focuses the air, for quick touch-ups and perfecting small details of your style.

Specifications

Caring technologies

ThermoShield technology
Ionic technology: 2x ions*

Attachments

Nozzle: 14 mm

Features

Heat/Speed settings: 6
Cool Shot
Storage hook

Technical specifications

Wattage: 2100 W
Motor: DC
Voltage: 220-240 V
Cord length: 1.8 m
Color / Finishing: White & Metallic

Service

2-year worldwide warranty

