

Video door phone

WelcomeEye Connect

Always connected by WIFI

Connected to your smartphone

7" touchscreen

Very high image quality



DES9900VDP



Touch screen and connected video doorphone With the WelcomeEye app

Protect and connect your home with the new Philips WelcomeEye Connect video doorphone. Don't miss a single visit thanks to this connected solution. Enjoy very high image quality with an elegant, high-end design.

Monitor your home wherever you are

- Intuitive tactile interface
- White LEDs for perfect night vision
- Monitor access to your home with the monitoring function
- Intercommunication between monitors in the same family
- Control access to your house from your smartphone

Optimal ease of use

- RFID tag to open your gate
- Ultra-thin monitor with premium finish and signature LEDs
- The system adapts to your daily use

Sturdy and reliable

- Don't miss a single visit
- Refined design in a 100% touchscreen monitor
- Weatherproof intercom panel

Highlights

7" touchscreen

7" touchscreen allows you to respond to your visitors and open the door or gate as needed. Easily set your preferences (volume, ringtones, backlighting, etc.) with the new WelcomeEye Connect video doorphone.

Colour night vision

The CMOS lens, with an extra-wide viewing angle (H130 °/V90 °) and white LEDs for exceptional night vision of up to 2.5 m, allows you to recognise your guests even in the dark.

Monitor access to your home

Use your smartphone or your doorphone screen to observe what happens in front of your house with the WelcomeEye Connect monitoring function.

Photo and video recording

Save a record of visitors who rang at your door with the integrated photo saving (internal memory) and video recording (on microSD card) functions. You won't miss a thing with the WelcomeEye Connect video doorphone.

RFID access control

RFID badges allow you to open your door or/and electric gate depending on your needs. No need for an entry code. Your video doorphone can save up to 20 RFID badges.

Talk between monitors

Communicate within your home thanks to the intercom function on WelcomeEye monitors.

Touchscreen monitor

Forget clumsy buttons and enjoy the refined and extremely elegant style of your touchscreen.

Ultra-flat monitor

The design integrates your house perfectly with its ultra-thin monitor (15 mm) and unique signature LED technology.

Upgradeable system

Set up a complete access control system according to your needs and add an external unit, a camera, and two additional screens to secure your house

Waterproof intercom panel

Use your video doorphone even in bad weather conditions such as rain, storms or even snow and rest assured that your system will keep working.

WelcomeEye application

See, talk and grant access to your home with the WelcomeEye smartphone app, whether you are at home or on the go.

Specifications

Ringtone

Number of rings: 6

Noise level: 85 dB

Electrical connection

Modular power supply: Electrical board

Electrical features

Electrical characteristics: 24V DC / 550mA / 13.2W

Finish

Intercom panel: Black aluminium and aluminium

Monitor: Black plastic and aluminium

Intercom panel

Door control: 12 V/2A max.

Illuminated call button

Illuminated name plate

Installation: Surface mounted

Lens: Not adjustable

Night vision: White LEDs (2.5 m)

RFID: 125 kHz - 20 badges max.

Sensor: C-MOS colour 900TVL

Viewing angle: H130°/V90°

Strike plate control: 12 V/1.1 A max.

Kit features

Dimensions: 210 (h) x 315 (l) x 78 (d) mm

Maximum distance

Wi-Fi: 2.4 GHz Wi-Fi network

Wired: 120 m

Operating temperature

Temperature range: -20°C / +50°C

Screen features

Diagonal: 7" (18cm)

External memory: MicroSD 32 GB card (not incl.)

Installation: Wall

Resolution: 800 x 480 px

Wi-Fi: 2.4 GHz IEEE 8111 b/g/n

Single product features

Intercom panel dimensions: 168 (h) x 82 (l) x 38 (d) mm

Monitor dimensions: 142 (h) x 210 (l) x 15 (d) mm

Smartphone compatibility

Application: WelcomeEye

Notification: PUSH

OS compatibility: Android / iOS

Use

Intercom panel: Outdoor (IP44)

Monitor: Indoor

Warranty

Years: 2

Wiring

Circuit: 2-Wire

Access control

Options: Lock and gate

Standard and certification

Type: CE, RoHS, REACH

Settings

Image: Colour, brightness, contrast

Volume

