

# PHILIPS

## Steam iron

### 5000 Series

2400 W power

45 g/min continuous steam

180 g steam boost

SteamGlide Plus



DST5030/80



## Built to perform, day after day

SteamGlide Plus soleplate lasts 4 times longer\*

For great results day after day, you want an iron that never lets you down. With its anti-scratch SteamGlide Plus soleplate, high consistent steam output and integrated calc-clean, this high quality iron gives you performance that lasts.

#### Fast & powerful crease removal

- 2400 W to heat up quickly
- Steam output up to 45 g/min for strong, steady performance
- Up to 180 g steam boost blasts stubborn creases
- Vertical steaming for hanging fabrics

#### Long lasting performance

- Scratch resistant soleplate provides good gliding
- Built-in calc-clean slider, long-lasting steam performance
- Tested cord for maximum durability and safety

#### Comfortable ironing

- Drip-stop keeps garments spotless while ironing
- Comfortable, textured handle for easy grip

# Highlights

## 2400 W to heat up quickly



Delivers a fast warm-up and powerful performance.

## SteamGlide Plus soleplate



Our special SteamGlide Plus soleplate smoothly glides over any fabric. It's also non-stick, scratch-resistant and easy to clean.

## No more messy dripping



Our Drip Stop system lets you iron delicate fabrics at low temperatures with confidence. There's no need to worry about water droplets causing stains.

## Continuous steam up to 45g/min



Strong and consistent steam output to remove creases faster.

## Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium buildup, or limescale, and maintain peak performance.

## Comfortable handle



A textured handle ensures you a comfortable, ergonomic grip, so you can keep hold of the iron without ever slipping.

## Steam boost up to 180 g



Penetrates deeper into fabrics to easily remove stubborn creases.

## Quality-tested cord



All our steam iron cords are rigorously tested for maximum safety and durability.

## Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

# Specifications

## Easy to use

Drip Stop  
Water tank capacity: 320 ml  
Extra large filling hole  
Extra stable heel rest  
Soleplate name: SteamGlide Plus  
Tap water suitable

## Fast crease removal

Continuous steam: 45 g/min  
Power: 2400 W  
Steam boost: 180 g  
Water spray

## Green efficiency

User manual: 100% recycled paper

## Guarantee

2 year worldwide guarantee

## Scale management

Descaling and cleaning: Built-in Calc Clean Slider

## Size and weight

Packaging dimensions (WxHxL):

33.2x16.7x13.7 cm

Product dimensions (WxHxL):

31.2x14.7x12.7 cm

Weight of iron: 1.255 kg

