

PHILIPS

DiamondFlex hard floors nozzle

Rotates 180° around objects

Universal fitting

With connection adapter



FC8076/01



Flexible cleaning in hard to reach areas with 180° rotation

The DiamondFlex nozzle rotates 180° to make it easier for you to clean around objects and in narrow spaces. The nozzle is ideal for hard floors, and has a universal fitting thanks to the connection adapter provided.

Flexible cleaning for difficult areas

- Rotates 180° to reach around objects and in narrow spaces
- Side air channels to clean along walls
- Suitable for hard floors

Compatible with most vacuum cleaners

- A connection adapter makes the nozzle universally fitting


Highlights

Rotates 180° around objects



The DiamondFlex nozzle is an ideal tool for reaching around objects, difficult to reach corners and narrow spaces. The nozzle has a 180° rotating mechanism and a memory function which ensures it automatically returns to its initial position.

Side air channels



The DiamondFlex nozzle is equipped with side air channels, to improve the cleaning performance alongside walls and furniture.

Suitable for hard floors



The nozzle is suitable to operate on all types of hard floors like parquet, tiles or vinyl.

Universal fitting



The nozzle is provided together with a connection adapter. Thus, it is compatible with Philips, Miele, Electrolux, AEG, Bosch, Siemens, Samsung, Rowenta, Hoover, LG, Panasonic, Zelmer models and many other vacuum cleaners with 32 or 35 mm connection.

Specifications

Accessory specifications

Number of nozzles: 1
Number of adaptors: 1

Usability

Tube coupling: Universal, Conical

Suitable for

EasyLife: FC8130 - FC8139, FC8140 - FC8149

EasyGo: FC8082 - FC8083

CompactGo: FC8120, FC8121, FC8291

PowerLife: FC8320 - FC8329, FC8450 - FC8459

2000 Series, PowerGo: FC8293 - FC8296, FC8240 - FC8246, FC8250, FC8253, FC8289

3000 Series, Performer Compact: FC8383 - FC8391, FC8370 - FC8379, FC8366 - FC8367 (A+)

5000 Series, PerformerActive: FC8650 - FC8664, FC8580 - FC8593, FC8520 - FC8527, FC8574 - FC8579, FC8563

Jewel: FC9050 - FC9079

Performer: FC9150 - FC9179, FC8680 - FC8682

PerformerPro: FC9180 - FC9199

Performer Expert: FC8720 - FC8728

7000 Series, Performer Silent: FC8779 - FC8786, FC8741 - FC8745

Performer Ultimate: FC8921 - FC8925, FC8941 - FC8957

SilentStar: FC9300 - FC9319

PowerPro Compact: FC8370 - FC8379, FC8515 - FC8517, FC9320 - FC9329, FC9330 - FC9334, FC9350 - FC9353

PowerPro Active: FC8630 - FC8649, FC9520 - FC9525, FC8670 - FC8679, FC9528 - FC9533, FC9540, FC9541

PowerPro: FC8760 - FC8767, FC8769, FC8770

PowerPro Expert: FC9712 - FC9714, FC9720 - FC9725, FC9728, FC9732 - FC9735, FC9729, FC9741 - FC9746

PowerPro Ultimate: FC9911 - FC9912, FC9919 - FC9934

Marathon: FC9200 - FC9225

Aqua Action: FC8950 - FC8952

Sustainability

Packaging: > 90% recycled materials

