

PHILIPS

Vacuum cleaner
with bag

PowerLife

1500 W

TriActive nozzle

FC8453/91



Full performance

Less energy consumption

Great cleaning results on all floors with the Philips PowerLife vacuum cleaner thanks to the unique TriActive nozzle.

Long lasting dust pickup

- 3 liter s-bag for long-lasting performance

Excellent cleaning results

- The TriActive nozzle applies 3 cleaning actions in one go

Ergonomic grip for far reach

- Reach all corners thanks to the extra long ergonomic grip

Lightweight metal telescopic tube

- Comfortable cleaning thanks to the lightweight aluminum tube

Highlights

3 liter s-bag

This large Philips dust bag capacity allows you to make optimal use of your vacuum cleaner bag, which means you have to change your dust bag less frequently.

Aluminum telescopic tube

The lightweight, aluminum vacuum cleaner tube is comfortable to use and carry. The 2-piece telescopic tube can be easily adjusted to your preferred height.

Extra long ergonomic grip

This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

TriActive nozzle

The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

Specifications

Performance

Airflow (max): 37 l/s
Annual energy consumption: 52 kW·h
Input power (IEC): 1400 W
Input power (max): 1500 W
Sound power level: 85 dB
Vacuum (max): 23,5 kPa

Usability

Action radius: 8 m
Carrying handle: Front
Cord length: 5 m
Tube type: Aluminum telescopic tube
Wheel type: Plastic
Tube coupling: Conical

Design

Color: Star Blue

Filtration

Dust bag type: s-bag
Dust capacity: 3 L
Exhaust filter: Microfilter

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
Accessory storage: On tubeclip
Standard nozzle: TriActive nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 406 x 282 x 220 mm
Weight of product: 4.2 kg

