

PHILIPS

Bagless vacuum
cleaner

PowerPro Compact

PowerCyclone 4 technology

Hard floors nozzle

FC9321/09



Full performance

Less energy consumption

The new Philips PowerPro Compact delivers full cleaning performance on all hard floors, thanks to the PowerCyclone 4 technology and the dedicated hard floors nozzle. The dust bucket is easy to empty, with no dust clouds.

Excellent cleaning results

- PowerCyclone 4 technology separates dust and air in one go
- Nozzle for optimal cleaning on all hard floors

Convenience

- Reach all corners thanks to the extra long ergonomic grip
- Advanced dust container design for easy to emptying

Clean air filter system

- EPA10 filter system with AirSeal for healthy air

Highlights

PowerCyclone 4 Technology



PowerCyclone 4 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

Hard floors nozzle




The Hard floors nozzle ensures optimal cleaning on all hard floors, especially on parquet and tiles. 1) The special soft brush hairs protect the floors against scratches. 2) The soft bristles pattern ensures optimal dust collection on all hard floors. 3) The nozzle is lightweight and equipped with wheels for great maneuverability on all floors.

Easy to empty dust container



The dust container is perfectly designed to dispose dust without creating a dust cloud. Thanks to its unique shape and smooth surface, dust is collected at one side of the container and evenly glides into the dust bin.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

EPA10 Clean air system



EPA10 filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

Specifications

Performance

Annual energy consumption: 26.5 kW·h
 Sound power level: 79 dB
 Input power (IEC): 750 W
 Airflow (max): 28,4 l/s
 Vacuum (max): 17,4 kPa

Design

Color: Bright blue

Filtration

Dust capacity: 1.5 L
 Exhaust filter: Sponge
 Motor filter: EPA 10 washable filter

Usability

Action radius: 8 m
 Cord length: 5 m
 Tube type: Metal 2-piece telescopic tube
 Tube coupling: Conical
 Wheel type: Plastic
 Carrying handle: Front

Nozzles and accessories

Standard nozzle: Hard floors nozzle
 Accessories included: Crevice tool, Small nozzle
 Additional nozzle: Hard floor nozzle

Weight and dimensions

Weight of product: 4.5 kg
 Dimensions of product (LxWxH): 406 x 285 x 238 mm

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

