

PHILIPS

Bagless vacuum cleaner

Marathon Ultimate

Allergy filter

2,2L

FC9919/07



Removes more dust than any 2400W vacuum cleaner*

Mess free dust disposal

The new Philips Marathon Ultimate bagless vacuum cleaner stands for superior cleaning performance. PowerCyclone 7 enables exceptional dust and air separation. TriActiveMax nozzle is for excellent performance on all floors.

Superior performance

- A-class performance on hard floors
- PowerCyclone 7 keeps strong suction power for longer
- Multi-Purpose nozzle
- Ultra Clean Air HEPA 13 filter with 99.95% filtration

Mess free dust disposal

- Extra Ergonomic Dust Bucket for controlled emptying



asimpleswitch.com

Highlights

A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

PowerCyclone 7



The aerodynamic design of PowerCyclone 7 minimizes air resistance and ensures exceptional cleaning performance through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

TriActiveMax nozzle



TriActiveMax nozzle perfectly seals to the floor and performs 3 actions in one go to thoroughly clean your floors: 1) A specially designed sole

plate gently opens the carpet and removes the dust from deep down. 2) Larger front opening pick up bigger particles. 3) Side brushes ensure perfect cleaning along the plinths.

Extra Ergonomic Dust Bucket



The side of the bucket has a specially designed spout-like shape. This enables to empty the bucket in a controlled manner without spilling the dust.

Ultra Clean Air HEPA 13 filter



The Ultra Clean Air HEPA 13 filter captures at least 99.95% of all dust, ensuring a clean & allergen-free environment.

Specifications

Performance

Airflow (max): 27 l/s
 Annual energy consumption: 26.7 kW·h
 Input power (IEC): 650 W
 Sound power level: 75 dB
 Vacuum (max): 17 kPa

Usability

Action radius: 11 m
 Carrying handle: Top and front
 Cord length: 8 m
 Tube type: Metal 2-piece telescopic tube
 Wheel type: Rubber
 Tube coupling: SmartLock
 Power control: Electronic on appliance

Design

Color: Full red

Filtration

Dust capacity: 2.2 L
 Exhaust filter: HEPA13 filter
 Motor filter: Lifetime washable filter

Nozzles and accessories

Accessories included: Crevice tool, 2-in-1 brush/small nozzle
 Additional nozzle: Hard floor nozzle
 Standard nozzle: TriActiveMax nozzle

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 506 x 310 x 317 mm
 Weight of product: 6.2 kg
 Dimensions of packaging (LxWxH): 595 x 400 x 352 mm



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

