

# PHILIPS

Bagless vacuum cleaner

Marathon Ultimate

Allergy filter

2,2L NanoClean

Super Turbo brush

FC9923/07



Removes more dust than any 2400W vacuum cleaner\*

Mess free dust disposal

The new Philips Marathon Ultimate bagless vacuum cleaner stands for superior cleaning performance. PowerCyclone 7 enables exceptional dust and air separation. TriActiveMax nozzle is for excellent performance on all floors.

#### Superior performance

- A-class performance on hard floors
- PowerCyclone 7 keeps strong suction power for longer
- Multi-Purpose nozzle
- SuperTurbo Brush for pet hair-free carpets
- Ultra Clean Air HEPA 13 filter with 99.95% filtration

#### Mess free dust disposal

- NanoClean Technology for mess free dust disposal
- Extra Ergonomic Dust Bucket for controlled emptying

#### Effortless cleaning

- Adjustable, long reach tool for hard-to-reach places



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

## PowerCyclone 7



The aerodynamic design of PowerCyclone 7 minimizes air resistance and ensures exceptional cleaning performance through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

## TriActiveMax nozzle



TriActiveMax nozzle perfectly seals to the floor and performs 3 actions in one go to thoroughly clean your floors: 1) A specially designed sole

plate gently opens the carpet and removes the dust from deep down. 2) Larger front opening pick up bigger particles. 3) Side brushes ensure perfect cleaning along the plinths.

## SuperTurbo Brush



Super TurboBrush perfectly removes pet hair from carpets.

## Ultra Clean Air HEPA 13 filter



The Ultra Clean Air HEPA 13 filter captures at least 99.95% of all dust, ensuring a clean & allergen-free environment.

## NanoClean Technology



The new innovative technology is especially developed to prevent the usual dust cloud. The new innovative technology is especially developed to prevent the usual dust cloud.

dust settles at the bottom of the dust bucket rather than staying in the air. When the bucket is opened there is no usual dust cloud.

## Extra Ergonomic Dust Bucket



The side of the bucket has a specially designed spout-like shape. This enables to empty the bucket in a controlled manner without spilling the dust.

## Extra long reach

Our long reach tool helps you clean high shelves or cupboard tops, with an adjustable brush for precision performance.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Performance

Airflow (max): 27 l/s

Annual energy consumption: 26.7 kW·h

Input power (IEC): 650 W

Sound power level: 75 dB

Vacuum (max): 17 kPa

## Usability

Action radius: 11 m

Carrying handle: Top and front

Cord length: 8 m

Tube type: Aluminium 2-P telescopic tube

Wheel type: Rubber

Tube coupling: SmartLock

Power control: Electronic on appliance

## Design

Color: Titanium

## Filtration

Dust capacity: 2.2 L

Exhaust filter: HEPA13 filter

Motor filter: Lifetime washable filter

## Nozzles and accessories

Accessories included: Crevice tool, 2-in-1 brush/small nozzle

Additional nozzle: Hard floor nozzle, Super Turbo brush

Extra accessories: Long reach tool

Standard nozzle: TriActiveMax nozzle

## Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

## Weight and dimensions

Dimensions of product (LxWxH): 506 x 310 x 317 mm

Weight of product: 6.2 kg

Dimensions of packaging (LxWxH): 595 x 400 x 352 mm

