

# PHILIPS

Bagless vacuum cleaner

Marathon Ultimate

AAA Energy Label\*

Allergy filter

2,2L NanoClean

Super Parquet

FC9924/07



Removes more dust than any 2400W vacuum cleaner\*

Mess free dust disposal

The new Philips Marathon Ultimate bagless vacuum cleaner stands for superior cleaning performance. PowerCyclone 7 enables exceptional dust and air separation. TriActiveMax nozzle is for excellent performance on all floors.

#### Superior performance

- High performance with 3AAA energy ratings
- A-class performance on hard floors
- PowerCyclone 7 keeps strong suction power for longer
- Multi-Purpose nozzle
- TriActive Z hard floor nozzle for dust and crumbs
- Ultra Clean Air HEPA 13 filter with 99.95% filtration

#### Mess free dust disposal

- NanoClean Technology for mess free dust disposal
- Extra Ergonomic Dust Bucket for controlled emptying

#### Effortless cleaning

- ErgoGrip remote control for No - bend Play and Pause



asimpleswitch.com

# Highlights

## 3AAA Energy rating



Engineered to achieve full performance with an A rating for energy efficiency, A on hard floor cleaning performance and A on dust re-emission.

## A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

## PowerCyclone 7




The aerodynamic design of PowerCyclone 7 minimizes air resistance and ensures exceptional cleaning performance through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

## TriActiveMax nozzle



TriActiveMax nozzle perfectly seals to the floor and performs 3 actions in one go to thoroughly clean your floors: 1) A specially designed sole plate gently opens the carpet and removes the dust from deep down. 2) Larger front opening pick up bigger particles. 3) Side brushes ensure perfect cleaning along the plinths.

## TriActive Z hard floor nozzle



The new TriActive Z hard floor nozzle removes all dust and crumbs in one go. Unique Z-shaped design guides the dust and the bigger crumbs into the air channel without pushing them forward. Side air channels perfectly clean along the plinths. Now there is no more need to lift the nozzle to remove bigger crumbs and ensure an exceptional clean of your hard floors.

## Ultra Clean Air HEPA 13 filter



The Ultra Clean Air HEPA 13 filter captures at least 99.95% of all dust, ensuring a clean & allergen-free environment.

## NanoClean Technology



The new innovative technology is especially developed to prevent the usual dust cloud. The new innovative technology is especially developed to prevent the usual dust cloud. The dust settles at the bottom of the dust bucket rather than staying in the air. When the bucket is opened there is no usual dust cloud.

## Extra Ergonomic Dust Bucket



The side of the bucket has a specially designed spout-like shape. This enables to empty the bucket in a controlled manner without spilling the dust.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Performance

**Airflow (max):** 27 l/s  
**Annual energy consumption:** 26.7 kW·h  
**Input power (IEC):** 650 W  
**Sound power level:** 75 dB  
**Vacuum (max):** 17 kPa

## Usability

**Action radius:** 11 m  
**Carrying handle:** Top and front  
**Cord length:** 8 m  
**Tube type:** Aluminium 2-P telescopic tube  
**Wheel type:** Rubber  
**Tube coupling:** SmartLock  
**Power control:** Remote control

## Design

**Color:** Bright copper

## Filtration

**Dust capacity:** 2.2 L  
**Exhaust filter:** HEPA13 filter  
**Motor filter:** Lifetime washable filter

## Nozzles and accessories

**Accessories included:** Crevice tool, 2-in-1 brush/small nozzle  
**Additional nozzle:** Hard floor nozzle, TriActiveZ nozzle  
**Extra accessories:** Remote control  
**Standard nozzle:** TriActiveMax nozzle

## Sustainability

**Packaging:** > 90% recycled materials  
**User manual:** 100% recycled paper

## Weight and dimensions

**Dimensions of product (LxWxH):** 506 x 310 x 317 mm  
**Weight of product:** 6.2 kg  
**Dimensions of packaging (LxWxH):** 595 x 400 x 352 mm

