

PHILIPS

Steam Iron with
OptimalTEMP technology

Azur Advanced

3000W

55 g/min continuous steam

230g steam boost

SteamGlide Advanced soleplate



GC4936/00



New generation iron for great results faster* Guaranteed no burns

Iron everything from jeans to silk with no risk of burning* thanks to OptimalTEMP technology and the steam output now penetrates up to 20% deeper into the fabric for faster crease removal.*

Intelligent ironing for ultimate convenience

- OptimalTEMP technology: Guaranteed no burns, no settings

Easier and faster ironing

- 3000 W for quick heat-up and powerful performance
- Deep penetrating steam, for great results faster
- 55g steam penetrates up to 20% more steam through fabric*
- Up to 230g steam boost blasts stubborn creases

Comfortable ironing

- SteamGlide Advanced soleplate, ultimate gliding & durability
- Smart calc reminder to remove calc from the iron
- Automatic shut-off when the iron is left unattended

Highlights

OptimalTEMP technology



Thanks to OptimalTEMP technology, we guarantee this iron will never cause burns to any ironable fabric and you can iron everything from jeans to silk, from linen to cashmere safely, in any order, without waiting for the temperature to adjust or pre-sorting clothes. Philips steam irons with OptimalTEMP makes your ironing easier and faster and has been tested by independent textile experts .

3000 W for fast heat up



Delivers a fast warm-up and powerful performance to get your ironing done quickly

Deep, penetrating steam

Thanks for the special design for maximum steam penetration, now up to 20%* more steam through the fabric for great results, faster

Continuous steam up to 55g/min



Strong and consistent steam output now penetrates up to 20% more steam through fabric to remove creases faster.

Steam boost up to 230 g



Penetrates deeper into fabrics to easily remove stubborn creases.

SteamGlide Advanced soleplate



Our superior SteamGlide Advanced soleplate delivers smooth gliding performance on any fabric. Its stainless steel base is twice as hard

as a aluminum, and our patented 6-layer coating with its advanced titanium layer effortlessly glides on any fabric for the fastest results.

Smart calc-clean reminder



This iron has a smart calc-clean reminder which indicates when the descaling is needed. Simply push the calc-clean button on the water tank to flush away the calc from the iron for long-lasting steam performance

Auto shut-off



The iron shuts itself off if you leave it standing still. On its soleplate, it will automatically switch off after 30 seconds. On its heel rest, it will automatically switch off after 8 minutes.

Specifications

Technology

OptimalTEMP technology

Fast crease removal

Continuous steam: 55 g/min

Power: 3000 W

Steam boost: 230 g

Vertical steam

Easy to use

Soleplate name: SteamGlide Advanced

Water tank capacity: 330 ml

Extra stable heel rest

Power cord length: 2,5 m

Drip stop

Extra large filling hole

Auto shut-off

Scale management

Descaling and cleaning: Self clean

Size and weight

Product dimensions (WxHxL): 33.3 x 17.5 x 13.5 cm

Guarantee

2 year worldwide guarantee

Green efficiency

User manual: 100% recycled paper

