

PHILIPS

Garment Steamer

Easy Touch

1500 W

Adjustable pole

3 steam settings



GC507/60



Easy crease removal every day

With powerful continuous steam and steam settings

EasyTouch garment steamer is designed for easy crease removal everyday. Watch the creases disappear easily thanks to the powerful steam, adjustable pole, steam level selection and a useful garment hanger.

Quick crease removal

- Powerful continuous steam
- 3 steam levels for different types of garments
- XL steam plate for quick results

Easy to use

- Special garment hanger
- Easy Rinse descaling function
- Detachable watertank
- Adjustable pole for various height settings

Maximum safety

- Glove for extra protection during steaming
- Safe to use on delicate fabrics, like silk
- PVC free silicon steam hose



Highlights

Powerful continuous steam



Powerful continuous steam is blown through the nozzles, enabling you to remove creases with only a few strokes.

Safe on all garments



The steamer is safe to use on all fabrics. It is a great solution for delicate fabrics like silk.

Easy Rinse descaling function



Prolong the lifetime of your appliance by using the Easy Rinse descaling function regularly.

Detachable watertank




Large, detachable, transparent water tank suitable for a long steaming session. Easy refill with large filling hole.

3 steam settings



Set your preferred steam level for optimal results on different kinds of garments.

Adjustable pole



Integrated adjustable pole for hanging your garments while using the steamer. It is collapsible for easy storage.

XL steam plate



The special ergonomic steamer head has an XL steam plate which helps you achieve results quickly.

PVC free silicon steam hose



The steam hose is made of silicon material which is the safe and healthy choice for use with steam. As the safety and health of your family is important, no PVC is used in the steam hose.

Glove for extra protection



Included is a glove that protects your hand during steaming.

Special garment hanger



Special garment hanger lets you easily hang your garments like shirts, dresses and trousers while using the steamer.

Specifications

Fast crease removal

Continuous steam: 30 g/min

Power: 1500 W

Variable steam: 3 levels

Variable steam levels

Voltage: 220 V

Easy to use

Safe on all ironable fabrics: Even delicates like silk

Water tank capacity: 1200 ml

Detachable water tank

Power cord length: 1.4 m

Accessories included

Garment hanger

Glove for extra protection

Guarantee

2 year worldwide guarantee

Scale management

Descaling and cleaning: Easy Rinse

