

PHILIPS

Handheld Steamer

8000 Series

Press-Steam laying or hanging

Steam up to 32g/min

De-Calc Technology

No Burns guaranteed



GC801/10



Powerful and convenient for quick results everyday

No ironing board needed!

The new Philips 8000 Series ensures quick and effortless de-wrinkling of your daily outfits; up to 5 garments at a time, no ironing board needed. It is safe to use on all fabrics, even delicate ones; no shine marks and no burns guaranteed.

Powerful and quick

- 32g/min powerful steam for quick results
- Ready to use in 60 seconds
- Heated plate for quick results

Effortless de-wrinkling

- Steam hanging your clothes or press-steam them laying
- Unique De-Calc Technology
- 230ml Water tank

Refresh clothes without washing or dry cleaning

- Steam kills up to 99.9% of bacteria*

Safe on all ironable fabrics

- No burns guaranteed with OptimalTemp technology

Highlights

Powerful and quick



Up to 32g/min powerful steam for quick results everyday.

Ready in 60 seconds



Ready to use in just 60 seconds.

Heated plate for quick results



Steam your outfit in as little as 3 minutes**. The heated plate prevents condensation on your garments for quick results.

Steam laying or hanging



Steam hanging clothes or press-steam them laying flat with our heated plate. No ironing board needed!

Unique De-Calc Technology



Thanks to the patented and unique De-Calc Technology, your appliance can last longer with the same steam performance.

230ml Water tank



12 minutes of non-stop steaming! The 230ml water tank enables you to steam up to 5 garments or two outfits without refill. More than enough for quick touch ups before leaving the house.

Steam kills 99.9% of bacteria*



Past few months made us look more for healthy and hygienic solutions. Our handheld steamer kills up to 99.9% of the bacteria*. You can even steam your curtains and bed sheets.

Safe on all ironable fabrics



No burns guaranteed with OptimalTemp technology. The steamer is safe to use on all fabrics. It is a great solution for delicate fabrics like silk and cashmere.

Specifications

Technology

For all ironable fabrics
No burns
OptimalTEMP technology

Fast crease removal

2-in-1 function
Power: 1600 W
Ready to use: 1 min
Steam-on-demand

Variable steam: 2 levels
Vertical steam
Voltage: 220 V

Easy to use

Water tank capacity: 230 ml
Drip Stop
Power cord length: 2.5-3 m
Ready to use: Light indicator
Refill any time during use
Silicone steam hose
Save on all fabrics: Even delicates like silk

Scale management

Descaling and cleaning: De-Calc Technology

Accessories included

Brush

Guarantee

2 year worldwide guarantee

