

PHILIPS

Car air purifier

GoPure SmartAir
330

App enabled smart air purifier

Fine particles
CADR*: 10m³/hour

Toxic gases CADR*: 10m³/hour

Air cleaning efficiency: 13min



GPSA33GPX1



Fresh and healthy air in your car with a simple touch on your phone

Enjoy fresh and healthy air in your car with Philips GoPure car air purifier. Pre-clean your car before your drive, to step into a fresh and clean air car. Track air quality in real time, to always know the air quality you breath.

Powerful air filtration

- Efficiently removes fine particles and toxic gases
- Cleans your car air in just 13 min

App enabled car air purifier

- Pre-clean your car air before your drive
- Always know the air quality you breath
- with life status and one click easy purchase

Refresh your air

- Refreshes your air with natural fragrance

Simplicity

- Automatic operations and filtration control
- Perfect in-car integration with installation in cup-holder

Highlights

Clean air efficiency



Boost-mode filtration cleans air quickly at highest speed

Pollution filtration

Philips unique high-efficiency filtration technology removes fine particles like PM2,5 with a Clean Air Delivery Rate (CADR) of 10m³/hour, and toxic gases with a CADR of 10m³/hour, to keep you and your family in good health.

Pre-clean your car air




With Philips GoPure smart car air purifier, you can pre-clean the air in your car when you are away, to step into a fresh and clean air car

Real-time air quality tracking




GoPure smart car air purifier track in real time indoor & outdoor air quality, and always let you know the air quality you breath

Filter replacement indicator



GoPure smart car air purifier displays the life status of the filter, and warns you when it is time to change it, to enjoy the best filtration efficiency, always

Natural fragrance dispenser



GoPure refreshes your air with natural fragrance dispensing function. 1 fragrance cartridge included

Automatic filtration



Focus on driving , thanks to automatic operations and filtration control

Easy installation



Including 4m 12V power cable and cup-holder installation accessory, for perfect in-car integration

Specifications

Product description

Air flow: 9.7 m³/h
Noise level: 40 (Low) - 50 (Mid) - 55 (High) dB
Air particle sensor
Air quality indicator (AQI)
Automatic On/Off
Filter replacement indicator
Fragrance dispenser
Frequency: 50 Hz
Speed settings: 3 speeds
Power: 7 W
Voltage: 12 V
Filter Lifetime: 350 hr
Technology: Car air purifier
Color: Black
Designation: GoPure Smartair 330
App enabled

Performance

Air Cleaning Efficiency: 13 min
Filtration bacteria/virus: 70 %
Boost mode
Toxic gases & TVOC filtration: CADR of 10m³/hour
Filtration of fine particles: CADR of 10m³/hour

Replacement

Fragrance cartridge: 51200X3, 51201X3, 51202X3
Filter type: GSF80X80X1

Weight and dimensions

Box dimensions (L x W x H): 295 x 245 x 80 mm
Product dimensions (L x W x H): 170 x 100 x

70 mm

Product weight: 800 g
Box weight (incl. product): 1200 g

Marketing specifications

Expected benefits: fresh healthy air in your car
Product highlight: fragrance dispenser, App enabled, Pre-cleaning

Accessories in the box

12v cigarette power cable: 4 m
Mounting accessories: Cup-holder kit
Other mounting accessories: Attachment belt

Logistic data

EAN (China): 6947939172269
Ordering code (China): 17226928
Quantity in box: 1
Reference (Order entry): GPSA33GPX1

